

**SAIS-M16-2/9****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M16 round plug-in connectors can transmit large amounts of power and have set the standard in the market for many years. The solder connection provides high contact density on a small area. With this technology the stripped conductor is soldered to the contacts, producing good electrical conductivity.

**General ordering data**

Version	Field attachable connector, M16, pin, straight
Order No.	<a href="#">1321700000</a>
Type	SAIS-M16-2/9
GTIN (EAN)	4050118125566
Qty.	1 pc(s).

## SAIS-M16-2/9

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	25 g
------------	------

## Technical data customisable plug-in connectors

Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Coding	none	Conductor cross-section, max.	0.75 mm <sup>2</sup>
Conductor cross-section, min.		Connection cross-section	0.14...0.75mm <sup>2</sup> (2-, 4-, 5-, 6-, 7- und 8-poles) / 0.14...0.25mm <sup>2</sup> (12- und 16-poles)
	0.14 mm <sup>2</sup>	Connection cross-section, min.	0.14 mm <sup>2</sup>
Connection cross-section, max.	0.75 mm <sup>2</sup>	Housing main material	PA
Contact surface	Ag (silver)	Number of poles	2
Insulation strength	10 <sup>8</sup> Ω	Pollution severity	3
Plugging cycles	≥ 500	Rated current	7 A
Protection degree	IP40	Rated voltage	250 V
Rated current	7 A (2-pole) / 6 A (4- and 5-pole) / 5 A (6-, 7- and 8-pole) / 3 A (12- and 16-pole)	Temperature range of housing	-40 ... +85 °C
Shield connection	No	Type of connection	Solder connection
Threaded ring material	Diecast zinc		

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02
ECLASS 14.0	27-44-01-16		

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
RoHS Compliance Status	Compliant

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

Creation date October 3, 2024 11:49:23 PM CEST

Catalogue status 28.09.2024 / We reserve the right to make technical changes.