

TM-I 12/18 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility. The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	TM-I, Insert markers, 30 x 4 mm, white
Order No.	1323730000
Type	TM-I 12/18 MC NE WS
GTIN (EAN)	4050118126785
Qty.	240 pc(s).
compatible printer	2715590000 2438520000 2438510000

TM-I 12/18 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	30 mm	Height (inches)	1.181 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.309 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Colour	white	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Insert markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40... 100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Orientation of print	horizontal and vertical	
Printed characters	neutral	
Recommended industries	Transportation, Machinery	
Type of printing	neutral	
UL 94 flammability rating	V-2	
Width	4 mm	

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Product Change Notification	DE - Technische Modifikation MultiCard Material EN - Technical change to MultiCard material Technical change to MultiCard material - DE Technical change to MultiCard material - EN MultiCard Material modification MultiCard Material Modification
Catalogues	Catalogues in PDF-format

TM-I 12/18 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

