

SFR 1/12 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The SlimFix Redesign SFR is a modification of the familiar SlimFix conductor marker which significantly simplifies installation. The marker is simply slid onto the cable and is securely fixed in no time.

General ordering data

| | |
|--------------------|--|
| Version | SlimFix R, Conductor and cable markers, 1.7 - 2.1 mm, 12 x 5.8 mm, white |
| Order No. | 1318640000 |
| Type | SFR 1/12 MC NE WS |
| GTIN (EAN) | 4050118124385 |
| Qty. | 400 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

SFR 1/12 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Height | 12 mm | Height (inches) | 0.472 inch |
| Width | 5.8 mm | Width (inches) | 0.228 inch |
| Net weight | 0.158 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|---|-----------|
| Colour | white | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Operating temperature range | -40...100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Recommended industries | Transportation, Machinery | |
| Size of labelling field | 12 x 3.2 mm | |
| UL 94 flammability rating | V-2 | |
| Width | 5.8 mm | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|----------------------------|
| Conductor O.D. | 1.7 - 2.1 mm | Conductor O.D., max. | 2.1 mm |
| Conductor O.D., min. | 1.7 mm | Conductor cross-section, max. | 0.75 mm ² |
| Conductor cross-section, min. | 0.5 mm ² | Cross-section for connected wire | 0.5 - 0.75 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

SFR 1/12 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| Product Change Notification | Technical change to MultiCard material - DE Technical change to MultiCard material - EN MultiCard Material modification MultiCard Material Modifikation |
| Catalogues | Catalogues in PDF-format |

SFR 1/12 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

