

WF 10/32**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The comprehensive range of stud terminals ensures secure connections for all power transmission applications. Connections range from 10 mm² to 300 mm². The connectors are attached to the threaded pins using crimped cable lugs and each connection is secured by tightening the hexagon nut. Stud terminals with threaded pins from M5 to M16 can be used according to the wire cross-section.

General ordering data

| | |
|------------|---|
| Version | Bolt-type screw terminals, Feed-through terminal, Rated cross-section: 120 mm ² , Threaded stud connection |
| Order No. | 1319070000 |
| Type | WF 10/32 |
| GTIN (EAN) | 4050118320077 |
| Qty. | 25 pc(s). |

WF 10/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 79 mm | Depth (inches) | 3.11 inch |
| Height | 67 mm | Height (inches) | 2.638 inch |
| Width | 32 mm | Width (inches) | 1.26 inch |
| Net weight | 88.12 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-----------------------------------|-----------------------|-------------------------------------|----|
| Version | Single-stud terminals | End cover plate required | No |
| Number of levels | 1 | Number of clamping points per level | 1 |
| Levels cross-connected internally | No | PE connection | No |
| Rail | TS 32 | | |

Additional technical data

| | | | |
|--------------------------|----|------------------|---------|
| Explosion-tested version | No | Type of mounting | Snap-on |
|--------------------------|----|------------------|---------|

Conductors for clamping (rated connection)

| | | | |
|---------------------------|--------------------------|--------------------------------|-------------------------|
| 2 x cable lugs DIN 46 234 | 6 to 120 mm ² | 2 x cable lugs DIN 46 235 | 10...95 mm ² |
| Cable lug to DIN 46234 | 6...120 mm ² | Cable lug to DIN 46235 | 10...95 mm ² |
| Clamping range, max. | 120 mm ² | Clamping range, min. | 6 mm ² |
| Number of connections | 1 | Stud size for spade connection | M 10 |
| Tightening torque, max. | 20 Nm | Tightening torque, min. | 10 Nm |
| Type of connection | Threaded stud connection | | |

General

| | |
|------|-------|
| Rail | TS 32 |
|------|-------|

Rating data

| | | | |
|--|---------------------|---|---------|
| Rated cross-section | 120 mm ² | Rated voltage | 1,000 V |
| Rated DC voltage | 1,000 V | Voltage with epoxy resin partition plate | 2,300 V |
| Rated current | 269 A | Current at maximum wires | 269 A |
| Volume resistance according to IEC 60947-7-x | 0.12 mΩ | Rated impulse withstand voltage | 8 kV |
| Impulse voltage with epoxy resin partition plate | 12 kV | Power loss in accordance with IEC 60947-7-x | 8.61 W |
| Pollution severity | 3 | | |

WF 10/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000897 | ETIM 7.0 | EC000897 |
| ETIM 8.0 | EC000897 | ETIM 9.0 | EC000897 |
| ECLASS 9.0 | 27-14-11-20 | ECLASS 9.1 | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-01 |
| ECLASS 14.0 | 27-25-01-01 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | CB Test Certificate CB Certificate CE Declaration of Conformity UKCA declaration of conformity Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |

WF 10/32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



WF 10/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.


- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/6 MC NE WS | Version |
| Order No. | 1609820000 | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190203436 | Weidmueller, white |
| Qty. | 1,000 pc(s). | |

Standard



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WQL 3 WF10 | Version |
| Order No. | 1781020000 | Bolt-type screw terminals, Cross-connector, Number of poles: 3 |
| GTIN (EAN) | 4032248241217 | |
| Qty. | 5 pc(s). | |

| | | |
|------------|----------------------------|--|
| Type | WQL 2 WF10 | Version |
| Order No. | 1781010000 | Bolt-type screw terminals, Cross-connector, Number of poles: 2 |
| GTIN (EAN) | 4032248219421 | |
| Qty. | 5 pc(s). | |

WF 10/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WEW 35/2 | Version |
| Order No. | 1061200000 | End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C |
| GTIN (EAN) | 4008190030230 | |
| Qty. | 50 pc(s). | |

Cover profiles



Cover profiles provide protection against external impact on functional areas of the terminal blocks or in combination with our support brackets for the entire terminal strip. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HA ADP WF6/WF10 | Version |
| Order No. | 1781050000 | Bolt-type screw terminals, Cover profile, dark beige, 2.2 mm |
| GTIN (EAN) | 4032248241231 | |
| Qty. | 10 pc(s). | |
| Type | ADP WF10/WF12 | Version |
| Order No. | 1780940000 | Bolt-type screw terminals, Cover profile, Transparent, 1000 mm |
| GTIN (EAN) | 4032248241255 | |
| Qty. | 1 m | |

WF 10/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Step-down bridges



Reducing cross-connectors enable simple and fast connection of terminal blocks with different rated cross-sections.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SMSE WF10/2XM6 | Version |
| Order No. | 1868880000 | Bolt-type screw terminals, Busbar, Number of poles: |
| GTIN (EAN) | 4032248499755 | |
| Qty. | 10 pc(s). | |

WF / WFF-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WTW WF10/WF12 2300 | Version |
| Order No. | 1780920000 | Bolt-type screw terminals, Partition plate, grey, 2 mm |
| GTIN (EAN) | 4032248241149 | |
| Qty. | 20 pc(s). | |
| Type | WTW WF6-WF12 | Version |
| Order No. | 1781240000 | Bolt-type screw terminals, Partition plate, dark beige, 2.5 mm |
| GTIN (EAN) | 4032248241156 | |
| Qty. | 20 pc(s). | |
| Type | WTW WF10/WF12 | Version |
| Order No. | 1780890000 | Bolt-type screw terminals, Partition plate, dark beige, 3 mm |
| GTIN (EAN) | 4032248219391 | |
| Qty. | 20 pc(s). | |

WF 10/32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WS 15/5 MC NE WS | Version |
| Order No. | 1609880000 | WS, Terminal marker, 15 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190203504 | Allen-Bradley, white |
| Qty. | 480 pc(s). | |

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon[®] Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

| | | |
|------------|----------------------------|----------------------------|
| Type | BZT 1 ZA WS 10/5 | Version |
| Order No. | 1805520000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248 | |
| Qty. | 100 pc(s). | |

| | | |
|------------|----------------------------|----------------------------|
| Type | BZT 1 WS 10/5 | Version |
| Order No. | 1805490000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 pc(s). | |

WF 10/32**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****DEK 5/6****WS/ DEK**

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | |
|------------|----------------------------|--|
| Type | DEK 5/6 MM WS | Version |
| Order No. | 2007120000 | Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392104 | |
| Qty. | 600 pc(s). | |