


SM DIA 60-22 K MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Device markers, 60 x 60 mm, ø 60 - 22 mm, Siemens 3 SB, Eaton Moeller M22-PV, yellow
Order No.	1323750000
Type	SM DIA 60-22 K MC NE GE
GTIN (EAN)	4050118127010
Qty.	10 pc(s).
compatible printer	2715590000 2438520000 2438510000

SM DIA 60-22 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	60 mm	Height (inches)	2.362 inch
Width	60 mm	Width (inches)	2.362 inch
Diameter	22 mm	Net weight	10.3 g

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

General data

Application/manufacture	ø 60 - 22 mm, Siemens 3 SB, Eaton Moeller M22-PV		
Colour	yellow		
Halogen	No		
Material	Polyamide 66		
Number of markers per combination	1 MultiCard = Device markers		
Number of markers per packaging unit	Form of supply	MultiCard	
Operating temperature range	-40...60 °C		
Operating temperature range, max.	60 °C		
Operating temperature range, min.	-40 °C		
UL 94 flammability rating	V-2		
Version	Self-adhesive		
Width	60 mm		

Device markers

Diameter	22 mm	Halogen	No
----------	-------	---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format

SM DIA 60-22 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

