

**CC-M 15/45 AL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 15 x 45 mm, silver
Order No.	<a href="#">1327730000</a>
Type	CC-M 15/45 AL
GTIN (EAN)	4050118132601
Qty.	200 pc(s).

## CC-M 15/45 AL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	15 mm	Height (inches)	0.591 inch
Width	45 mm	Width (inches)	1.772 inch
Net weight	0.853 g		

## Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

## General data

Colour	silver	
Material	Anodized aluminium	
Number of markers per combination	1 MetalliCard = Device markers	
Number of markers per packaging unit	Form of supply	MetalliCard
Operating temperature range	-55...130 °C	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Recommended industries	Energy, Process	
Size of labelling field	15.2 x 42.2 mm	
Width	45 mm	

## Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### CC-M 15/45 AL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



**CC-M 15/45 AL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Complementary products****General ordering data**

Type INLAY CC-M UNIVERSAL

Order No. [1341120000](#)

GTIN (EAN) 4050118145458

Qty. 1 pc(s).

Type INLAY CC-M 15/45

Order No. [1341090000](#)

GTIN (EAN) 4050118145175

Qty. 1 pc(s).

Type PRIMER CC-M

Order No. [2068020000](#)

GTIN (EAN) 4050118416534

Qty. 100 pc(s).

Type DKB CC 15/45

Version

Order No. [1341170000](#)

MetalliCard, Adhesive strip, 15 x 45 mm, Transparent

GTIN (EAN) 4050118145441

Qty. 240 pc(s).