

CC-M DIA 30 ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	MetalliCard, Device markers, silver
Order No.	1327770000
Type	CC-M DIA 30 ST
GTIN (EAN)	4050118132632
Qty.	200 pc(s).

CC-M DIA 30 ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.5 mm	Depth (inches)	0.02 inch
Diameter	30 mm	Net weight	2.68 g

Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

General data

Colour	silver	
Material	Micro-etched stainless steel 1.4301 (ST), Stainless steel 1.4301	
Number of markers per combination	1 MetalliCard = Device markers	
Number of markers per packaging unit	Form of supply	MetalliCard
Operating temperature range	-55...130 °C	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Recommended industries	Energy, Process	
Size of labelling field	28.2 x 28.2 mm	

Device markers

Diameter	30 mm	Drill-hole diameter	4.2 mm
----------	-------	---------------------	--------

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

CC-M DIA 30 ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



CC-M DIA 30 ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Complementary products****General ordering data**

Type	INLAY CC-M DIA 30	
Order No.	1341100000	
GTIN (EAN)	4050118145199	
Qty.	1 pc(s).	
Type	DKB CC DIA 30	Version
Order No.	1341180000	MetalliCard, Adhesive strip, Transparent
GTIN (EAN)	4050118145618	
Qty.	200 pc(s).	
Type	INLAY CC-M UNIVERSAL	
Order No.	1341120000	
GTIN (EAN)	4050118145458	
Qty.	1 pc(s).	
Type	PRIMER CC-M	
Order No.	2068020000	
GTIN (EAN)	4050118416534	
Qty.	100 pc(s).	