



**LMFS 5.00/05/180 3.5SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The new LMF allows us to meet the current market requirements for a PCB terminal with PUSH IN connection system for wire cross-sections up to 2.5 mm<sup>2</sup>

- PUSH IN connection system
- LMF with pusher for opening the terminal point
- LMFS without pusher, the terminal point is opened with a screwdriver
- Integrated test point
- 90° and 180° wire outlet direction

**General ordering data**

|              |  |
|--------------|--|
| Version      | Printed circuit board terminals, 5.00 mm, Number of poles: 5, 180°, Solder pin length (l): 3.5 mm, tinned, orange, PUSH IN without actuator, Clamping range, max. : 2.5 mm², Box |
| Order No.    | <a href="#">1330470000</a>   |
| Type         | LMFS 5.00/05/180 3.5SN OR BX   |
| GTIN (EAN)   | 4050118134605  |
| Qty.         | 55 pc(s).  |
| Product data | IEC: 400 V / 24 A / 0.5 - 2.5 mm²<br>UL: 300 V / 20 A / AWG 24 - AWG 12  |
| Packaging    | Box  |

Creation date July 26, 2024 9:41:34 PM CEST

Catalogue status 13.07.2024 / We reserve the right to make technical changes.

## LMFS 5.00/05/180 3.5SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Depth                    | 14.8 mm    | Depth (inches)  | 0.583 inch |
| Height                   | 18.7 mm    | Height (inches) | 0.736 inch |
| Height of lowest version | 15.2 mm    | Width           | 27.7 mm    |
| Width (inches)           | 1.091 inch | Net weight      | 9.4 g      |

## System parameters

|  |                              |  |                          |
|--|------------------------------|--|--------------------------|
| Product family                               | OMNIMATE Signal - series LMF | Wire connection method                     | PUSH IN without actuator |
| Mounting onto the PCB                        | THT solder connection        | Conductor outlet direction                 | 180°                     |
| Pitch in mm (P)                              | 5 mm                         | Pitch in inches (P)                        | 0.197 "                  |
| Number of poles                              | 5                            | Pin series quantity                        | 1                        |
| Fitted by customer                           | No                           | Number of rows                             | 1                        |
| Max. adjacent poles per row                  | 24                           | Solder pin length (l)                      | 3.5 mm                   |
| Solder pin dimensions                        | d = 0.8 mm, 0.6 x 0.8 mm     | Solder eyelet hole diameter (D)            | 1.1 mm                   |
| Solder eyelet hole diameter tolerance (D)+   | 0.1 mm                       | Number of solder pins per pole             | 2                        |
| Screwdriver blade                            | 0.6 x 3.5                    | Screwdriver blade standard                 | DIN 5264                 |
| Stripping length                             | 10 mm                        | L1 in mm                                   | 20 mm                    |
| L1 in inches                                 | 0.787 "                      | Touch-safe protection acc. to DIN VDE 0470 | IP 20                    |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch       | Protection degree                          | IP20                     |

## Material data

|                                       |            |                                       |                  |
|---------------------------------------|------------|---------------------------------------|------------------|
| Insulating material                   | Wemid (PA) | Colour                                | orange           |
| Colour chart (similar)                | RAL 2000   | Comparative Tracking Index (CTI)      | ≥ 600            |
| UL 94 flammability rating             | V-0        | Contact material                      | Cu-alloy         |
| Contact surface                       | tinned     | Coating                               | 4-6 µm SN        |
| Tinning type                          | matt       | Layer structure of solder connection  | 4...8 µm Sn matt |
| Storage temperature, min.             | -40 °C     | Storage temperature, max.             | 70 °C            |
| Operating temperature, min.           | -50 °C     | Operating temperature, max.           | 120 °C           |
| Temperature range, installation, min. | -25 °C     | Temperature range, installation, max. | 120 °C           |

## Conductors suitable for connection

|   |                      |
|---|----------------------|
| Clamping range, min.                            | 0.2 mm <sup>2</sup>  |
| Clamping range, max.                            | 2.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.         | AWG 24               |
| Wire connection cross section AWG, max.         | AWG 12               |
| Solid, min. H05(07) V-U                         | 0.5 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                         | 2.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                      | 0.25 mm <sup>2</sup> |
| Flexible, max. H05(07) V-K                      | 2.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.25 mm <sup>2</sup> |
| w. plastic collar ferrule, DIN 46228 pt 4, max. | 2.5 mm <sup>2</sup>  |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.25 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, max.       | 2.5 mm <sup>2</sup>  |
| Plug gauge in accordance with EN 60999 a x b; ø | 2.4 mm x 1.5 mm      |

Creation date July 26, 2024 9:41:34 PM CEST

## LMFS 5.00/05/180 3.5SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                     |  |                              |                            |       |
|---------------------|--|------------------------------|----------------------------|-------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired                 |       |
|                     |  | nominal                      | 0.5 mm <sup>2</sup>        |       |
|                     | wire end ferrule                       | Stripping length             | nominal                    | 12 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H0.5/16 OR</a> |       |
|                     |  | Stripping length             | nominal                    | 10 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H0.5/10</a>    |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                 |       |
|                     |  | nominal                      | 0.75 mm <sup>2</sup>       |       |
|                     | wire end ferrule                       | Stripping length             | nominal                    | 12 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H0.75/16 W</a> |       |
|                     |  | Stripping length             | nominal                    | 10 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H0.75/10</a>   |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                 |       |
|                     |  | nominal                      | 1 mm <sup>2</sup>          |       |
|                     | wire end ferrule                       | Stripping length             | nominal                    | 12 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.0/16D R</a> |       |
|                     |  | Stripping length             | nominal                    | 10 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.0/10</a>    |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                 |       |
|                     |  | nominal                      | 1.5 mm <sup>2</sup>        |       |
|                     | wire end ferrule                       | Stripping length             | nominal                    | 10 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.5/10</a>    |       |
|                     |  | Stripping length             | nominal                    | 12 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.5/16 R</a>  |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                 |       |
|                     |  | nominal                      | 2.5 mm <sup>2</sup>        |       |
|                     | wire end ferrule                       | Stripping length             | nominal                    | 10 mm |
|                     |  | Recommended wire-end ferrule | <a href="#">H2.5/10</a>    |       |

Reference text Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)

## Rated data acc. to IEC

|   |                        |   |                   |
|---|------------------------|---|-------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 24 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 24 A                   | Rated current, min. number of poles (Tu=40°C)                         | 24 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 24 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 20 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 24 | Wire cross-section, AWG, max.     | AWG 12 |

Creation date July 26, 2024 9:41:34 PM CEST

## LMFS 5.00/05/180 3.5SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to UL 1059

Institute (cURus)



Certificate No. (cURus)

E60693

Rated voltage (Use group B / UL 1059) 300 V

Rated voltage (Use group D / UL 1059) 300 V

Rated current (Use group B / UL 1059) 20 A

Rated current (Use group D / UL 1059) 10 A

Wire cross-section, AWG, min. AWG 24

Wire cross-section, AWG, max. AWG 12

Reference to approval values  
Specifications are maximum values, details - see approval certificate.

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 338 mm |
| VPE width | 130 mm | VPE height | 27 mm  |

## Type tests

|                               |                |  |
|-------------------------------|----------------|--|
| Test: Durability of markings  | Test           | mark of origin, type identification, pitch, approval marking UL, durability        |
|                               | Evaluation     | passed   |
| Test: Clampable cross section | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02 |
|                               | Conductor type | Type of conductor and solid 0.14 mm <sup>2</sup> conductor cross-section           |
|                               |                | Type of conductor and stranded 0.14 mm <sup>2</sup> conductor cross-section        |
|                               |                | Type of conductor and solid 1.5 mm <sup>2</sup> conductor cross-section            |
|                               |                | Type of conductor and stranded 1.5 mm <sup>2</sup> conductor cross-section         |
|                               |                | Type of conductor and AWG 24/1 conductor cross-section                             |
|                               |                | Type of conductor and AWG 24/19 conductor cross-section                            |
|                               |                | Type of conductor and AWG 16/1 conductor cross-section                             |
|                               |                | Type of conductor and AWG 16/19 conductor cross-section                            |
|                               | Evaluation     | passed   |

## LMFS 5.00/05/180 3.5SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |                |   |
|---|----------------|---|
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00  |
|   | Requirement    | 0.2 kg  |
|   | Conductor type | Type of conductor and AWG 24/1 conductor cross-section                      |
|   |                | Type of conductor and AWG 24/19 conductor cross-section                     |
|   | Evaluation     | passed  |
|   | Requirement    | 0.3 kg  |
|   | Conductor type | Type of conductor and stranded 0.25 mm <sup>2</sup> conductor cross-section |
|   |                | Type of conductor and solid 0.5 mm <sup>2</sup> conductor cross-section     |
|   | Evaluation     | passed  |
|   | Requirement    | 0.4 kg  |
| Pull-out test   | Conductor type | Type of conductor and solid 1.5 mm <sup>2</sup> conductor cross-section     |
|   |                | Type of conductor and stranded 1.5 mm <sup>2</sup> conductor cross-section  |
|   | Conductor type | Type of conductor and AWG 16/1 conductor cross-section                      |
|   |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|   | Evaluation     | passed  |
|   | Standard       | DIN EN 60999-1 section 9.5 / 12.00  |
|   | Requirement    | ≥10 N   |
|   | Conductor type | Type of conductor and AWG 24/1 conductor cross-section                      |
|   |                | Type of conductor and AWG 24/19 conductor cross-section                     |
|   | Evaluation     | passed  |
|   | Conductor type | Type of conductor and stranded 0.25 mm <sup>2</sup> conductor cross-section |
|   |                | Type of conductor and H05V-K0.5 conductor cross-section                     |
|   | Evaluation     | passed  |
|   | Requirement    | ≥20 N   |
|   | Conductor type | Type of conductor and H07V-U1.5 conductor cross-section                     |
|   |                | Type of conductor and H07V-K1.5 conductor cross-section                     |
|   | Conductor type | Type of conductor and AWG 16/1 conductor cross-section                      |
|   |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|   | Evaluation     | passed  |
|   | Requirement    | ≥40 N   |
|   | Conductor type | Type of conductor and H07V-U1.5 conductor cross-section                     |
|   |                | Type of conductor and H07V-K1.5 conductor cross-section                     |
|   | Conductor type | Type of conductor and AWG 16/1 conductor cross-section                      |
|   |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|   | Evaluation     | passed  |
|   | Requirement    | ≥40 N   |
|   | Conductor type | Type of conductor and H07V-U1.5 conductor cross-section                     |
|   |                | Type of conductor and H07V-K1.5 conductor cross-section                     |
|   | Conductor type | Type of conductor and AWG 16/1 conductor cross-section                      |
|   |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|   | Evaluation     | passed  |

## LMFS 5.00/05/180 3.5SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002643    | ETIM 7.0    | EC002643    |
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ECLASS 9.0  | 27-44-04-01 | ECLASS 9.1  | 27-44-04-01 |
| ECLASS 10.0 | 27-44-04-01 | ECLASS 11.0 | 27-46-01-01 |
| ECLASS 12.0 | 27-46-01-01 | ECLASS 13.0 | 27-46-01-01 |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## Important note

|                |   |
|----------------|---|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.  |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• The test point can only be used as potential-pickup point.</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

## LMFS 5.00/05/180 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>  |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">FL ANALO.SIGN.CONV. EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION_EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## LMFS 5.00/05/180 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

## Drawings


## Product image




## Dimensional drawing



## Graph



## Graph



## Product benefits



Optional conductor outlet direction  
 Stable mechanical design

## Product benefits



High reliability of the current capacity



**LMFS 5.00/05/180 3.5SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Slotted screwdriver**

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

|            |                            |                          |
|------------|----------------------------|--------------------------|
| Type       | SDIS 0.6X3.5X100           | Version                  |
| Order No.  | <a href="#">9008390000</a> | Screwdriver, Screwdriver |
| GTIN (EAN) | 4032248056354              |                          |
| Qty.       | 1 pc(s).                   |                          |

**Additional accessories****No task is too small when creating the perfect solution.**

Connections form just one part of the overall process. Small details are often the key to the perfect solution in applications where potentials are tested, grouped or even isolated.

A system is not a system without small but essential details:

- Test plugs ensure reliable pick-up from diagnostic sockets

In tandem with the manufacturing process and application.

**General ordering data**

|            |                            |  |              |           |
|------------|----------------------------|--|--------------|-----------|
| Type       | PS 2.0 MC                  | Version  | Product data | Packaging |
| Order No.  | <a href="#">0310000000</a> | PCB plug-in connector, Accessories, Test plug, red, Number of poles: 1 |              | Box       |
| GTIN (EAN) | 4008190000059              |  |              |           |
| Qty.       | 20 pc(s).                  |  |              |           |

## LMFS 5.00/05/180 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

### Product benefits



Direct conductor entry  
Cross section up to 2.5 mm<sup>2</sup>

### Product benefits



Maintenance through test point







WEITERGABE SOWIE Vervielfaeltigung dieses Dokuments, Verwertung und MitteiluNG seines Inhalts sind verboten, soweit nicht ausdruecklich gestattet.  
ZuWiderhandlungen Verpflichten zu Schadenersatz. Alle Rechte fuer den Fall der Patent-, Gebrauchsmuster- oder geschmacksmustereintragung vorbehalten.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMUELLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.

© WEIDMUELLER INTERFACE GmbH & Co.KG

MASSE OHNE TOLERANZ SIND KEINE PRUEFMASSE  
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.

DIE DEUTSCHE VERSION IST VERBINDLICH  
THE GERMAN VERSION IS BINDING

ALLGEMEINGUELTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE  
GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED



P= 5.00 RASTER PITCH  
D=  $\varnothing 1.1 +0.1$   
0.043"  
d= 0.6x0.8  
0.024"x0.031"  
l= 3.5  
0.138"

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.  
Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.  
Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|         |         |           |
|---------|---------|-----------|
| 24      | 115.00  | 4.528     |
| 23      | 110.00  | 4.331     |
| 22      | 105.00  | 4.134     |
| 21      | 100.00  | 3.937     |
| 20      | 95.00   | 3.740     |
| 19      | 90.00   | 3.543     |
| 18      | 85.00   | 3.346     |
| 17      | 80.00   | 3.150     |
| 16      | 75.00   | 2.953     |
| 15      | 70.00   | 2.756     |
| 14      | 65.00   | 2.559     |
| 13      | 60.00   | 2.362     |
| 12      | 55.00   | 2.165     |
| 11      | 50.00   | 1.969     |
| 10      | 45.00   | 1.772     |
| 9       | 40.00   | 1.575     |
| 8       | 35.00   | 1.378     |
| 7       | 30.00   | 1.181     |
| 6       | 25.00   | 0.984     |
| 5       | 20.00   | 0.787     |
| 4       | 15.00   | 0.591     |
| 3       | 10.00   | 0.394     |
| 2       | 5.00    | 0.197     |
| n POLES | L1 [mm] | L1 [inch] |

|                                      |  |                                  |  |   |  |
|--------------------------------------|--|----------------------------------|--|---|--|
| GENERAL TOLERANCE:<br>DIN ISO 2768-m |  | 70657/4<br>26.06.13 TIELKER_S 01 |  | CAT.NO.: . . .  |  |
| RoHS COMPLIANT                       |  | MODIFICATION                     |  | <b>Weidmüller</b>   |  |
| DRAWN 25.01.2012 REGLIN_A            |  | DATE NAME                        |  | <b>LMF... 5.00/.../180 ...</b><br>LEITERPLATTENKLEMME<br>PCB TERMINAL |  |
| RESPONSIBLE SCHMITZ_T                |  |                                  |  |   |  |
| CHECKED 26.06.2013 HECKERT_M         |  |                                  |  |   |  |
| SCALE: 2/1                           |  | APPROVED HANKE_D                 |  | PRODUCT FILE: LMF 5.0X  |  |
| SUPERSEDES: .                        |  |                                  |  | 7403  |  |

## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.