

**PAC-UNIV-HE10-HE10-4M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Pre-assembled cable, PAC   |
| Order No.  | <a href="#">1349630040</a> |
| Type       | PAC-UNIV-HE10-HE10-4M      |
| GTIN (EAN) | 4032248249183              |
| Qty.       | 1 pc(s).                   |

## PAC-UNIV-HE10-HE10-4M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 181 g |
|------------|-------|

## Temperatures

|                     |             |                       |          |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

## General Data

|                    |                                 |                       |                                 |
|--------------------|---------------------------------|-----------------------|---------------------------------|
| Cable              | Cable LiYY                      | Cable length          | 4                               |
| Connector PLC side | FLAT CABLE CONECTOR<br>HE10 10P | Interface connector   | FLAT CABLE CONECTOR<br>HE10 10P |
| Material           | PVC                             | Number of poles, min. | 10-pole                         |
| Outer diameter     | 7 ± 1 mm                        | Suitable for          | Digital signals                 |
| Wire cross-section | 0.14 mm <sup>2</sup>            |                       |                                 |

## Electrical Data

|                        |                     |  |            |
|------------------------|---------------------|--|------------|
| Capacity wire / shield | 300 pF/m            | Capacity wire / wires                          | 300 pF/m   |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path,<br>max. | 1 A        |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                     | ≤ 150 mΩ/m |
| Total current, max.    | 3 A                 |  |            |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ECLASS 9.0  | 27-24-22-20 | ECLASS 9.1  | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|