

## PAC-UNIV-D50M-D50F-3M

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 14,2 ± 1 mm |
| Order No.  | <a href="#">1350000030</a>                         |
| Type       | PAC-UNIV-D50M-D50F-3M                              |
| GTIN (EAN) | 4032248278046                                      |
| Qty.       | 1 pc(s).   |

**PAC-UNIV-D50M-D50F-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |
|------------|---------|
| Net weight | 1,120 g |
|------------|---------|

**Temperatures**

|                     |             |                       |          |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

**General Data**

|                    |                      |                       |                  |
|--------------------|----------------------|-----------------------|------------------|
| Cable              | Cable LiYCY          | Cable length          | 3                |
| Connector PLC side | SUB-D FEMALE 50P     | Interface connector   | SUB-D MALE 50P   |
| Material           | PVC                  | Number of poles, min. | 50-pole          |
| Outer diameter     | 14,2 ± 1 mm          | Suitable for          | Analogue signals |
| Wire cross-section | 0.25 mm <sup>2</sup> |                       |                  |

**Electrical Data**

|                        |                     |   |           |
|------------------------|---------------------|---|-----------|
| Capacity wire / shield | 300 pF/m            | Capacity wire / wires                       | 300 pF/m  |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Total current, max.    | 3 A                 |   |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ECLASS 9.0  | 27-24-22-20 | ECLASS 9.1  | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|