

VPU II 2 R PV 600V DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Surge voltage arrester, Low voltage, with remote contact
Order No.	1351370000
Type	VPU II 2 R PV 600V DC
GTIN (EAN)	4050118158717
Qty.	1 pc(s).
Replacement parts	1351320000 1402570000

VPU II 2 R PV 600V DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	69 mm	Depth (inches)	2.717 inch
Height	106 mm	Height (inches)	4.173 inch
Width	35.6 mm	Width (inches)	1.402 inch
Mounting dimension - height	75 mm	Net weight	0.304 g

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70
---------------------	----------------	-----------------------	-------------

Connection data, remote alert

Connection type	PUSH IN	Cross-section for connected wire, solid core, max.	1.5 mm ²
Cross-section for connected wire, solid core, min.	0.14 mm ²	Stripping length	8 mm

General data

Colour	black, orange	Design	Installation housing; 2TE, Insta IP 20
Operating altitude	≤ 2000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20	Rail	TS 35
UL 94 flammability rating	V-0	Version	with remote contact

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Discharge current I_n (8/20 μs)	12.5 kA	Discharge current, max. (8/20 μs)	40 kA
Maximum continuous operating voltage DC UCPV mode +/-, -/PE, +/-PE	600 V	Operating height in the grounded PV system	≤ 2000 m
Operating height in ungrounded PV system	≤ 2000 m	PV system voltage, max. U_{cpv}	600 V
Protection level U_p (+/-)	≤ 4.4 kV	Protection level U_p (+/PE)	≤ 2.2 kV
Protection level U_p (-/PE)	≤ 2.2 kV	Requirements class	Type II
Short-circuit current I_{SCP}	200 A	Standards	EN 50539-11
Total discharge current I_{total} (8/20 μs)	40		

Rated data IEC / EN

Discharge current I_n (8/20 μs) wire-PE	20 kA	Discharge current, max. (8/20 μs)	40 kA
Leakage current at U_n	30 μA	Max. continuous voltage, U_c (DC)	600 V
Number of poles	2	PV voltage, acc. to IEC 60364-7-712	< 600 V
Rated voltage (DC)	600 V	Response time	≤ 25 ns
SPD type	T2	Signalling contact	250 V 1A 1CO, 125 V AC / 1 A, 48 V CC / 0.5 A, 24 V DC / 0.5 A
Standards	EN 50539-11	Voltage type	DC

VPU II 2 R PV 600V DC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data

Stripping length	15 mm	Type of connection	Screw connection
Stripping length, rated connection	15 mm	Tightening torque, min.	2 Nm
Tightening torque, max.	3 Nm	Clamping range, rated connection	16 mm ²
Clamping range, min.	1.5 mm ²	Clamping range, max.	35 mm ²
Wire cross-section, solid, min.	1.5 mm ²	Wire cross-section, solid, max.	16 mm ²
Wire connection cross section, finely stranded, min.	1.5 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	1.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	50 mm ²
Connection cross-section, stranded, min.	1.5 mm ²	Connection cross-section, stranded, max.	50 mm ²

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

Tender specification sheets

Long specification	<p>Multi-pole surge voltage arrester according to the requirements of Class II acc. to IEC 50539-11. Consisting of V0 material, the arrester serves as overvoltage protection and is used in applications according to IEC 50539-12. The use of a high-performance varistor meets the inspection requirements for Class II surge protection systems on the basis of the standards. The arrester is installed in the vicinity of the equipment that needs protection, in a commercially available installation/electrical distribution enclosure. With thermal separation device on the varistor. If protection is no longer available, the colour in the display window changes from green to red. The functional state is also displayed by a voltage-free signalling contact (CO contact). Rated voltage: 600 VDC In/max (8/20 µs): 20/40 kA, protection level < 2.2 kV, telecommunication output: contact: 250 V/0.5 A 48 VDC/0.1 A, type: Weidmüller VPU II 2 R PV 600 V/40 kA, Order No. 1351370000 or equivalent</p>	<p>Short specification</p> <p>Class II arrester with In/Imax: 20/40 kA suitable for PV systems. Protection level < 2.2 kV. With remote alert Type: Weidmüller VPU II 2 R PV 600 V/40 kA Order no. 1351370000 or equivalent</p>
--------------------	---	---

VPU II 2 R PV 600V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EU_Konformitätserklärung / EU_Declaration_of_Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures


VPU II 2 R PV 600V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Electric symbol



Circuit diagram

VPU II 2 R PV 600V DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Crosshead screwdriver Phillips**

VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	

VPU II 2 R PV 600V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Replacement parts**VPU Series**

Extensive accessories round off the product range

General ordering data

Type	PLUG VPU	Version
Order No.	1402570000	VPU series, Accessories
GTIN (EAN)	4050118204360	
Qty.	10 pc(s).	

Spare Arrester**General ordering data**

Type	VPU II 0 PV 600V DC	Version
Order No.	1351320000	Surge voltage arrester, Low voltage, Accessories
GTIN (EAN)	4050118158755	
Qty.	1 pc(s).	