

VPU I 0 LCF 280V/12,5KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Spare arrester Type I**

Weidmüller VPU I surge protection products protect low-voltage consumer installations and electronic devices against overvoltages that can occur as a result of atmospheric discharges (thunderstorms) or switching operations (transients). The VPU I series meets the Type I and Type II requirements acc. to IEC 61643-11 and the Type 1 and Type 2 requirements acc. to EN 61643-11. The spare arresters are coded and can only be inserted into suitable bases.

General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester
Order No.	1352000000
Type	VPU I 0 LCF 280V/12,5KA
GTIN (EAN)	4050118158212
Qty.	1 pc(s).

VPU I 0 LCF 280V/12,5KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	52 mm	Height (inches)	2.047 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	141 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70
Humidity	5 - 95% rel. humidity		

General data

Colour	orange	Design	Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Segment	Power distribution	UL 94 flammability rating	V-0
Version	Spare arrester		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

Rated data IEC / EN

Discharge current I_{\max} (8/20 μ s) wire-PE	50 kA	Discharge current I_n (8/20 μ s) wire-PE	25 kA
Follow-on current extinguishing capability I_{fi}	Not available due for technical reasons	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary ≤ 250 A gG, 250 A gL (if back up fuse > 250 A)
Leakage current at U_n	1 μ A	Lightning test current I_{imp} (10/350 μ s) (L-PE)	12.5 kA
Max. continuous voltage, U_c (AC)	280 V	Number of poles	1
Protection level U_p at I_N (L/N-PE)	≤ 1.45 kV	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Response time	≤ 100 ns	Short-circuit current rating I_{SCCR}	25 kA
Standards	IEC61643-11, EN61643-11	Temporary surge voltage (over-voltage) - TOV	438 V
Voltage type	AC		

Connection data

Type of connection	pluggable
--------------------	-----------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

VPU I 0 LCF 280V/12,5KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Tender specification sheets**

Long specification	Spare arrester for VPU I 0 280 V LCF-series surge voltage arrester with 12.5 kA. The pluggable high-performance varistors made from V0 material can be replaced by trained personnel following a failure. Rated voltage: 280 V LCF Type: Weidmüller VPU I 0 LCF 280 V/12.5 kA Order No.: 1352000000	Short specification	Spare arrester for surge voltage arrester VPU I 0 280 V LCF series with 12.5 kA. The pluggable high-performance varistors can be swapped by trained personnel following a failure. Rated voltage: 280 V LCF Type: Weidmüller VPU I 0 LCF 280 V/12.5 kA Order no.: 1352000000
--------------------	---	---------------------	--

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EU_Konformitätserklärung / EU_Declaration_of_Conformity](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)


VPU I 0 LCF 280V/12,5KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Electric symbol



Schematic circuit diagram

VPU I 0 LCF 280V/12,5KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Crosshead screwdriver Phillips




VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH1 X 80	Version
Order No.	2749890000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118897098	
Qty.	1 pc(s).	

Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 1.0X5.5X125	Version
Order No.	2749850000	Screwdriver, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade
GTIN (EAN)	4050118897050	thickness (A): 1 mm
Qty.	1 pc(s).	