

VPU II 0 150V/40KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Spare arrester Type II**

Weidmüller VPU II surge protection products protect low-voltage consumer installations and electronic devices against overvoltages that can occur as a result of atmospheric discharges (thunderstorms) or switching operations (transients). The VPU II series meets the Type II and Type III requirements acc. to IEC 61643-11:2012 and Type 2 and Type 3 requirements acc. to EN 61643-11:2012. The spare arresters are coded and can only be inserted into suitable bases.

General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester
Order No.	1352450000
Type	VPU II 0 150V/40KA
GTIN (EAN)	4050118157864
Qty.	1 pc(s).

VPU II 0 150V/40KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	52 mm	Height (inches)	2.047 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	83 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70
Humidity	5 - 95% rel. humidity		

General data

Colour	orange	Design	Installation housing; 1TE, Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Rail	TS 35	UL 94 flammability rating	V-0
Version	Spare arrester		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Rated data IEC / EN

Combined pulse U_{OC}	10 kV	Discharge current I_n (8/20 μ s) wire-PE	20 kA
Energy coordination (≤ 10 m)	Type II, Type III	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	125 A gL > (if back up fuse > 125 A), No Fuse necessary ≤ 125 A gG
Leakage current at U_n	30 μ A	Max. continuous voltage, U_c (AC)	150 V
Number of poles	1	Protection level U_p at I_N (L/N-PE)	≤ 0.9 kV
Rated voltage (AC)	120 V	Requirements category acc. to IEC 61643-11	Type II, Type III
Requirements class, acc. to EN 61643-11	T2, T3	Response time	≤ 25 ns
Short-circuit current rating I_{SCCR}	25 kA	Standards	IEC61643-11, EN61643-11
Temporary surge voltage (over-voltage) - TOV	228 V	Voltage type	AC

Connection data

Type of connection	pluggable
--------------------	-----------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

VPU II 0 150V/40KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Tender specification sheets**

Long specification	Spare arrester consisting of V0 material for surge voltage arrester VPU II 150 V series The pluggable high-performance varistors can be exchanged by trained personnel following a failure. Rated voltage: 150 V Type: Weidmüller VPU II 0 150 V/30 kA Order No.: 1352450000	Short specification	Spare arrester for surge voltage arrester VPU II 150 V series The pluggable high-performance varistors can be swapped by trained personnel following a failure. Rated voltage: 150 V Type: Weidmüller VPU II 0 150 V/30 kA Order no.: 1352450000
--------------------	--	---------------------	--

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EU Konformitätserklärung / EU Declaration of Conformity](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

VPU II 0 150V/40KA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Electric symbol

