

**KLIPPON COPL 165609****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

**General ordering data**

Version	Klippon POK (polyester empty enclosure), Earthing plate, Miscellaneous, Height: 60.5 mm, Width: 656 mm, Depth: 0.8 mm, Material: Brass, polished, untreated
Order No.	<a href="#">1391020000</a>
Type	KLIPPON COPL 165609
GTIN (EAN)	4050118191134
Qty.	5 pc(s).

**KLIPPON COPL 165609****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	60.5 mm	Height (inches)	2.382 inch
Width	656 mm	Width (inches)	25.827 inch
Wall thickness, min.	0.8 mm	Wall thickness, max.	0.8 mm
Net weight	50 g		

**General information**

Material	Brass	Material thickness	0.8 mm
Surface finish	polished, untreated		

**Classifications**

ETIM 6.0	EC002623	ETIM 7.0	EC002623
ETIM 8.0	EC002623	ETIM 9.0	EC002623
ECLASS 9.0	27-18-28-14	ECLASS 9.1	27-18-92-64
ECLASS 10.0	27-18-28-14	ECLASS 11.0	27-18-28-14
ECLASS 12.0	27-18-28-14	ECLASS 13.0	27-18-28-14
ECLASS 14.0	27-18-28-14		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	