

TBY-SAI143-F-L-PS-2KS-Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Analogue interfaces are equipped with 40-pole connectors (KS). Versions are available with disconnecting plugs and test points which are extremely useful for voltage and current measurements. There are also versions with useful additional pins for customers who wish to incorporate other elements (resistor ...) for converting voltage/current or monitoring the current loop.

General ordering data

Version	Interface, RS, 2 x KS (40P), LM3NZF 5.08mm
Order No.	1371250000
Type	TBY-SAI143-F-L-PS-2KS-Z
GTIN (EAN)	4050118207125
Qty.	1 pc(s).

TBY-SAI143-F-L-PS-2KS-Z
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Technical data
Dimensions and weights

Depth	107 mm	Depth (inches)	4.213 inch
Height	131 mm	Height (inches)	5.157 inch
Width	133 mm	Width (inches)	5.236 inch
Net weight	403.4 g		

Temperatures

Storage temperature	-40...85 °C	Operating temperature	-25...70 °C
---------------------	-------------	-----------------------	-------------

General data

LED status display per channel	red	Disconnection per channel	No
Type of test point	No	Switch	No
Fuse per channel	1 A	LED status of the supply voltage	green
Power supply fuse	6.3 A		

Connection data

Connection (field side)	LM3NZF 5.08mm	Connection on control side	2 x KS (40P)
Connection supply	LMNZF 5.08mm	Number of poles (control side)	40-pole plug

Ratings data

Operating voltage	24 V DC	Max. current for common pole	1 A
Max. current per channel	1 A		

Insulation coordination (EN50178)

Rated insulation voltage	< 50 V AC	Surge voltage category	III
Pollution severity level	2	Pulse voltage test (1,2/50µs)	0.8 kV
Insulation test voltage AC	0.35 kV		

Connection field

Clamping range, max.	2.5 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	1.5 mm ²	Flexible with sleeve, min.	0.25 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Max. wire cross-section, AWG	AWG 14	Min. wire cross-section, AWG	AWG 24
Sleeve with plastic collar, max.	1.5 mm ²	Solid, max. H05(07) V-U	2.5 mm ²
Solid, min. H05(07) V-U	0.2 mm ²	Stripping length	7.5 mm
Type of connection	Tension-clamp connection		

Supply connection

Type of connection	Tension-clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Ferrule with plastic collar, max.	1.5 mm ²
Wire cross-section, min. AWG	AWG 14	Wire cross-section, max. AWG	AWG 24
Stripping length	7.5 mm		

TBY-SAI143-F-L-PS-2KS-Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-14-11-52
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

Approvals

Approvals

**Downloads**

Catalogues [Catalogues in PDF-format](#)

Brochures

www.weidmueller.com