


## KLIPPON COPL 162609

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

|            |   |
|------------|---|
| Version    | Klippon POK (polyester empty enclosure), Earthing plate, Miscellaneous, Height: 60.5 mm, Width: 339 mm, Depth: 0.8 mm, Material: Brass, polished, untreated |
| Order No.  | <a href="#">1391000000</a>  |
| Type       | KLIPPON COPL 162609   |
| GTIN (EAN) | 4050118191318   |
| Qty.       | 5 pc(s).  |

## KLIPPON COPL 162609

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|                      |         |                      |             |
|----------------------|---------|----------------------|-------------|
| Depth                | 0.8 mm  | Depth (inches)       | 0.031 inch  |
| Height               | 60.5 mm | Height (inches)      | 2.382 inch  |
| Width                | 339 mm  | Width (inches)       | 13.346 inch |
| Wall thickness, min. | 0.8 mm  | Wall thickness, max. | 0.8 mm      |
| Net weight           | 26 g    |                      |             |

### General information

|                |                     |                    |        |
|----------------|---------------------|--------------------|--------|
| Material       | Brass               | Material thickness | 0.8 mm |
| Surface finish | polished, untreated |                    |        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002623    | ETIM 7.0    | EC002623    |
| ETIM 8.0    | EC002623    | ETIM 9.0    | EC002623    |
| ECLASS 9.0  | 27-18-28-14 | ECLASS 9.1  | 27-18-92-64 |
| ECLASS 10.0 | 27-18-28-14 | ECLASS 11.0 | 27-18-28-14 |
| ECLASS 12.0 | 27-18-28-14 | ECLASS 13.0 | 27-18-28-14 |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |