

CS1,6E14-12 AU,75 I3,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

For a reliable contact - CB/CS crimp contact.

The combination of RSV housings and Weidmüller's crimp contacts enable custom adaptations to the specific requirements of your applications.

The following product options are available depending on the system:

- Safe centring of the contacts using the three-segment pin tips
- High contact reliability using four defined contact points
- Locking clasp in the cantilever spring for a secure mount of the contacts in the housing
- Pin contacts with two lengths to implement leading-pin contacts
- Up to 100 plugging cycles (tin version)
- Up to 500 plugging cycles (gold version)

The appropriate high-quality tools from Weidmüller guarantee professional processing.

General ordering data

Version	PCB plug-in connector, Crimp contact, Individual contact, Pin – standard, Gold-plated, Max. clamping range : 2.5 mm ²
Order No.	1428600000
Type	CS1,6E14-12 AU,75 I3,5
GTIN (EAN)	4008190078867
Qty.	250 pc(s).
Product data	
Packaging	Box

CS1,6E14-12 AU,75 I3,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.58 g
------------	--------

System Parameters

Wire connection method	Crimp connection	Conductor outlet direction	180°
Number of poles	1	Volume resistance	4.80 mΩ
Stripping length	4 mm		

Material data

Contact material	Cu-alloy	Contact surface	Gold-plated
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Conductors suitable for connection

Clamping range, max.	2.5 mm ²	Wire connection cross section AWG, min.	AWG 14
Wire connection cross section AWG, max.	AWG 12	Solid, min. H05(07) V-U	1.5 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Stranded, min. H07V-R	1.5 mm ²
Stranded, max. H07V-R	2.5 mm ²	Flexible, min. H05(07) V-K	1.5 mm ²
Flexible, max. H05(07) V-K	2.5 mm ²	w. wire end ferrule, DIN 46228 pt 1, min.	0 mm ²
w. wire end ferrule, DIN 46228 pt 1, max.	0 mm ²	Outer diameter of insulation, min.	2.8 mm
Outer diameter of insulation, max.	3.5 mm		

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated impulse voltage for surge voltage class/ pollution degree III/2	0 kV
-------------------------	------------------------	---	------

Packing

Packaging	Box	VPE length	97 mm
VPE width	90 mm	VPE height	40 mm

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-04-92	ECLASS 9.1	27-44-04-92
ECLASS 10.0	27-44-04-92	ECLASS 11.0	27-46-04-03
ECLASS 12.0	27-46-04-03	ECLASS 13.0	27-46-04-03

Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
----------------	--

Notes	<ul style="list-style-type: none"> The long pins can be used with the standard pins as leading contacts. Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months
-------	---

Creation date May 29, 2024 2:00:16 PM CEST

CS1,6E14-12 AU,75 I3,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS

Conform

DownloadsApproval/Certificate/Document of Con-
formity[Declaration of the Manufacturer](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[MB DEVICE MANUF. EN](#)[FL 72H SAMPLE SER EN](#)[PO OMNIMATE EN](#)[PO OMNIMATE EN](#)

CS1,6E14-12 AU,75 I3,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Dimensional drawing



CS1,6E14-12 AU,75 I3,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Contact removal tools



Weidmüller offers a variety of crimping tools, contact removal tools, and fibre optic tools.

General ordering data

Type	DW RSV 1.6	Version
Order No.	9004530000	Tool miscellaneous, Release tool
GTIN (EAN)	4008190041991	
Qty.	1 pc(s).	

Crimping tools



Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF RSV 12	Version
Order No.	9013550000	Pressing tool, Crimping tool for contacts, FoderBcrimp
GTIN (EAN)	4008190002046	
Qty.	1 pc(s).	
Type	HTF RSV 16	Version
Order No.	9013560000	Pressing tool, Crimping tool for contacts, FoderBcrimp
GTIN (EAN)	4008190161163	
Qty.	1 pc(s).	