

THM WO 15/70 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 9.6 - 12.7 mm, 15 x 70 mm, white
Order No.	1429440000
Type	THM WO 15/70 WS
GTIN (EAN)	4050118233872
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.591 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	112 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	
Approval acc. to UL 969	Yes	
Colour	white	
Halogen	No	
Material	Polyester film	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	500	
Operating temperature range	-40...150 °C	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Size of labelling field	30 x 15 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	70 mm	

Conductor and cable markers

Conductor O.D.	9.6 - 12.7 mm	Conductor O.D., max.	12.7 mm
Conductor O.D., min.	9.6 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 120 mm ²
Halogen	No	Text field height	30 mm
Text field width	15 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads


Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Drawings



THM WO 15/70 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	