

RJ45C5 T1U 2.8N4N TY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The product range encompasses the following designs:

- 90°, lying (horizontal) and 180°, standing (vertical)
- latch up / latch down
- THT, THR or SMD soldering processes
- Wide range of different design types, also with integrated LEDs and shield contact tabs
- Performance category Cat. 3 to Cat. 6
- Packed either in a tray (TY) or on a roll (tape-on-reel, RL)
- Compatible with modular RJ45 connector according to ANSI / TIA-1096-A and IEC 60603
- Dielectric strength ≥ 1500 V AC RMS (2250 V AC peak value) according to IEEE 802.3
- Dielectric strength ≥ 1500 V AC (peak value) or ≥ 1500 V DC according to IEC 60603

Properties and advantages:

- Extended temperature range of -40°C to $+85^{\circ}\text{C}$ for maximum performance
- Reinforced gold layer ($30\mu\text{m}$) for improved corrosion protection
- At least 0.3mm stand-off ensures a perfect soldering result

General ordering data

| | |
|------------|---|
| Version | PCB plug-in connector, RJ45 jacks, Cat. 5 , THT solder connection, 90°, Latch option: top, Shield tabs: none, 30...80 μm Ni / $\geq 30 \mu\text{m}$ Au , LED: No, Number of poles: 8, Tray |
| Order No. | 1455240000 |
| Type | RJ45C5 T1U 2.8N4N TY |
| GTIN (EAN) | 4050118261356 |
| Qty. | 140 pc(s). |
| Packaging | Tray |

RJ45C5 T1U 2.8N4N TY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|-----------------|------------|
| Depth | 15.71 mm | Depth (inches) | 0.619 inch |
| Height | 15.86 mm | Height (inches) | 0.624 inch |
| Height of lowest version | 13.11 mm | Width | 16.41 mm |
| Width (inches) | 0.646 inch | Net weight | 2.436 g |

System specifications

| | | | |
|--|--------------|---------------------------------|-----------------------------------|
| Category | Cat. 5 | LED | No |
| Latch option | top | Mounting onto the PCB | THT solder connection |
| Number of poles | 8 | Number of solder pins per pole | 1 |
| Outgoing elbow | 90° | Performance-Category | Cat. 5 |
| Pitch in inches (P) | 0.05 " | Pitch in mm (P) | 1.27 mm |
| Plugging cycles | 750 | Product family | OMNIMATE Data - RJ45 modular jack |
| Protection degree | IP20 | Shield surface | nickel-plated |
| Shield tabs | none | Shielding | Yes |
| Shielding material | Copper alloy | Solder eyelet hole diameter (D) | 0.9 mm |
| Solder eyelet hole diameter tolerance (D) ± 0.1 mm | | Solder pin dimensions | 0.40 x 0.30 mm |
| Solder pin length (l) | 2.75 mm | Soldering process | Manual soldering, Wave soldering |
| Tolerance of solder pin position | ± 0.1 mm | Type of connection | Solder connection |
| Wiring | 8-core | | |

Electrical properties

| | | | |
|--|-----------|---------------------------------------|----------------------------|
| Dielectric strength, contact / contact | 1000 V DC | Dielectric strength, contact / shield | 1500 V DC |
| Insulation strength | ≥ 500 MΩ | PoE / PoE+ | conforming to IEEE 802.3at |
| Rated current | 1.5 A | Rated voltage | 125 V |

Standards

| | |
|--------------------|----------------|
| Connector standard | IEC 60603-7-51 |
|--------------------|----------------|

Material data

| | | | |
|----------------------------------|----------------------------|-----------------------------|-------------------|
| Insulating material | PA 66 | Colour | black |
| Colour chart (similar) | RAL 9011 | Insulating material group | II |
| Comparative Tracking Index (CTI) | ≥ 500 | Insulation strength | ≥ 500 MΩ |
| UL 94 flammability rating | V-0 | Contact base material | Phosphorus bronze |
| Contact material | Cu-alloy | Contact surface | Gold over nickel |
| Layer structure of plug contact | 30...80 μ" Ni / ≥ 30 μ" Au | Storage temperature, min. | -40 °C |
| Storage temperature, max. | 85 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 85 °C | | |

Packing

| | | | |
|-----------|--------|------------|--------|
| Packaging | Tray | VPE length | 319 mm |
| VPE width | 189 mm | VPE height | 66 mm |

RJ45C5 T1U 2.8N4N TY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002637 | ETIM 7.0 | EC002637 |
| ETIM 8.0 | EC002637 | ETIM 9.0 | EC002637 |
| ECLASS 9.0 | 27-44-04-02 | ECLASS 9.1 | 27-44-04-02 |
| ECLASS 10.0 | 27-44-04-02 | ECLASS 11.0 | 27-46-02-01 |
| ECLASS 12.0 | 27-46-02-01 | ECLASS 13.0 | 27-46-02-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

Approval/Certificate/Document of Conformity

[Certificate of Compliance](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[PCN](#)[PCN](#)

User Documentation

[MAN IE GUIDE DE](#)[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)




Brochures

[MB FREECONTACT EN](#)[FL FIELDWIRING EN](#)[PI PROFINET CABLING EN](#)[PI PROFINET CABLING EN](#)

RJ45C5 T1U 2.8N4N TY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Drawings

RJ45C5 T1U 2.8N4N TY







Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings



Detailed drawing



www.weidmueller.com


Recommended wave soldering profiles

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Single Wave:



Double Wave:



Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.