

SAISW-3+PE/11-S-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Field attachable connector, M12, pin, 90°
Order No.	1467860000
Type	SAISW-3+PE/11-S-COD
GTIN (EAN)	4050118273410
Qty.	1 pc(s).

SAISW-3+PE/11-S-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	27 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	8...10 mm (PG11)	Cable diameter, max.	10 mm
Cable diameter, min.	8 mm	Cable glands	PG 11
Coding	S-coded	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.14 mm ²	Connection cross-section, max.	2.5 mm ²
Connection cross-section, min.	0.14 mm ²	Contact material	CuZn
Contact surface	Gold-plated	Housing main material	PA
Insulation strength	10 ⁸ Ω	Number of poles	4
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	12 A
Rated current	12 A	Rated voltage	630 V
Shield connection	No	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Screw connection

General Info

Number of poles	4	Connection 1	M12
Connection 2	Screw	Housing main material	PA
Connection thread	M12	Contact material	CuZn
Contact surface	Gold-plated	Protection degree	IP67
Plugging cycles	≥ 100		

Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4
RoHS Compliance Status	Compliant

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

SAISW-3+PE/11-S-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAISW-3+PE/11-S-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Pole scheme**