

**IE-FCI-D9-FS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Signal insert D-Sub, 9-pole, Socket / solder connection
Order No.	<a href="#">1450870000</a>
Type	IE-FCI-D9-FS
GTIN (EAN)	4050118255393
Qty.	1 pc(s).

## IE-FCI-D9-FS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	15.3 mm	Height (inches)	0.602 inch
Width	12.5 mm	Width (inches)	0.492 inch
Length	30.8 mm	Length (inches)	1.213 inch
Net weight	7.919 g		

## Temperatures

Operating temperature	-55 °C...105
-----------------------	--------------

## Technical data

Contact resistance	≤ 20 mΩ	Contact surface	Gold-plated
Current-carrying capacity	1 A	Dielectric strength, contact / contact	1 kV <sub>eff</sub> / 1 min.
Housing main material	SPCC	Housing surface	tin-plated
Insulation strength	1000 MΩ at 500 V DC	Material insulator	PBT glass fibre reinforced UL 94 V-0
Number of poles	9		

## General data

Insert type	Signal insert D-Sub, 9-pole	Protection degree	IP20
-------------	-----------------------------	-------------------	------

## Electrical properties

Contact resistance	≤ 20 mΩ	Dielectric strength, contact / contact	1 kV <sub>eff</sub> / 1 min.
Insulation strength	1000 MΩ at 500 V DC		

## General standards

Certificate No. (DNV)	TAA000022B
-----------------------	------------

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-18-90-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-18-28-92	ECLASS 13.0	27-18-28-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

## Approvals

Approvals



ROHS	Conform
------	---------

Creation date May 23, 2024 4:21:20 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

## IE-FCI-D9-FS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[GL\\_FrontCom](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[MB FREECONTACT EN](#)

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)


## IE-FCI-D9-FS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing



### Dimensioned drawing

