

**H2,5/16T GR BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

- Linked wire-end ferrules on reel (5,000 pcs.)
- DIN colour code
- other colour code

**General ordering data**

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 12 mm, 10 mm, grey |
| Order No.  | <a href="#">1476120000</a>                     |
| Type       | H2,5/16T GR BD GSP                             |
| GTIN (EAN) | 4050118283020                                  |
| Qty.       | 3,000 pc(s).                                   |
| Packaging  | Reel   |

**H2,5/16T GR BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |
|------------|---------|
| Net weight | 0.201 g |
|------------|---------|

**Technical data**

| Description of article | Reel of wire end ferrules, grey | Version | Standard |
|------------------------|---------------------------------|---------|----------|
|------------------------|---------------------------------|---------|----------|

**Wire-end ferrules**

|                             |                     |   |               |
|-----------------------------|---------------------|---|---------------|
| Collar diameter (D2)        | 4.2 mm              | Colour code                             | Telemecanique |
| Conductor cross-section     | 2.5 mm <sup>2</sup> | Contact surface diameter (D1)           | 2.2 mm        |
| Contact surface length (L2) | 10 mm               | L1 in mm                                | 16 mm         |
| Metal sleeve thickness (S1) | 0.15 mm             | Plastic collar thickness (S2)           | 0.25 mm       |
| Stripping length            | 12 mm               | Wire connection cross section AWG, max. | AWG 14        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ECLASS 9.0  | 27-40-02-01 | ECLASS 9.1  | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

**Approvals**

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E354986    |

**Downloads**

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">Technical information - EN</a><br><a href="#">Technical information - DE</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>   |

**H2,5/16T GR BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**