

KSPMH M40 BSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration****IEC EX**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSPMH (Klippon blanking plug, type MH), Blanking plug, straight, M 40, 16 mm, Brass
Order No.	1477790000
Type	KSPMH M40 BSC
GTIN (EAN)	4050118285475
Qty.	10 pc(s).

KSPMH M40 BSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	21.5 mm	Height (inches)	0.846 inch
Length	21.5 mm	Length (inches)	0.846 inch
Diameter	40 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	15 mm	Net weight	232.7 g

Temperatures

Operating temperature	-60 °C...200 °C
-----------------------	-----------------

Certificate numbers cable gland

Approval conditions	ATEX, IECEX	Certificate no. cable gland (ATEX)	SIRA 09ATEX1320X or CML 19ATEX1089X
Certificate no. cable gland (IECEX)	IECEX SIR 09.0131X or IE- CEX CML 19.0022X	Identification	Ex d IIC Gb, Ex e IIC Gb, Ex tb IIIC Db

KSPMH M40 BSC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General information

Diameter of sealing ring	40 mm	External thread	M 40
Halogen	halogen-free	Impact resistance	7 J ATEX version
Length of thread	16 mm	Material	Brass
Note: protection class	<ul style="list-style-type: none"> • All metric sealing plugs have a thread pitch of 1.5 mm. • In Ex nR applications, the KSPMH must be fitted with a further seal. • To obtain the specified IP rating, the through hole must comply with the regulations of EN 50262 Table 1 and it should be possible to secure the sealing plug in a suitable manner. • Operating instructions are enclosed with each sealing plug; these must be read prior to installation. The sealing plugs must be installed according to the specifications in the operating instructions. • On installation of the KSPMH, the minimum number of engaged thread turns in line with the standard EN/IEC 60079-1, Section 5.3, must be observed. • With NEC / CEC applications, it must be ensured that the inner thread of the connection device into which the sealing plugs are screwed reveals at least 8 fully engaged thread turns. • If KSPMH sealing plugs are inserted into non-metallic Ex e connection devices, they must be connected to the system's earth circuit. 		
O.D.	45.5 mm	Operating temperature range, max.	200 °C
Operating temperature range, min.	-60 °C	Protection class (UL)	Type 4X
Protection degree	IP66, IP68 (100 m / 168 h)	Silicone	Yes
Standards	EN 60079-31, EN 60079-0, EN 60079-1, EN 60079-7	Tightening torque	10 Nm
Water depth	100 m		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-35
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

KSPMH M40 BSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC

Lead 7439-92-1

SCIP

8dcc5b23-3a47-4c75-bd2c-bcb18becee86

Approvals

ROHS

Conform

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)