

CC-M DIA 30 AL SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	MetalliCard, Device markers, silver
Order No.	1474410000
Type	CC-M DIA 30 AL SDR
GTIN (EAN)	4050118290806
Qty.	1 pc(s).

CC-M DIA 30 AL SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Diameter	30 mm	Net weight	0.96 g

Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

General data

Colour	silver		
Material	Chrome coated aluminium (AL), Anodized aluminium		
Number of markers per combination	1 MetalliCard = Device markers		
Number of markers per packaging unit	Form of supply	MetalliCard	
Operating temperature range	-55...130 °C		
Operating temperature range, max.	130 °C		
Operating temperature range, min.	-55 °C		
Printed characters	Based on customer requirements (Please send M-Print PRO file)		
Size of labelling field	28.2 x 28.2 mm		

Device markers

Diameter	30 mm	Drill-hole diameter	4.2 mm
----------	-------	---------------------	--------

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CC-M DIA 30 AL SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

