

**PAC-C300-1616-50-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The pre-wired cables allow connecting the Honeywell C300 IOTAs (Input Output Terminal Assemblies) and the Weidmüller FTAs (Field Terminal Assemblies) in a manner that is quick, simple and error free.

The cables may be delivered with single or dual connectors, or even with free ends and end ferrules.

The hood makes it easier to handle and it offers a robust connection with the IOTA. It also allows using cables of different gauge sizes and lengths of up to 50m.

**General ordering data**

Version	Cable LiYCY, 0.50 mm <sup>2</sup>
Order No.	<a href="#">1481630030</a>
Type	PAC-C300-1616-50-3M
GTIN (EAN)	4099986584648
Qty.	1 pc(s).

**PAC-C300-1616-50-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0 g

**Temperatures**

Storage temperature -10...60 °C Operating temperature -10...50 °C

**General Data**

Cable	Cable LiYCY	Cable length	3 m
Connector PLC side	SP-BLZ 5.08/16/180	Interface connector	SP-BLZ 5.08/16/180
Material	PVC	Number of poles, min.	16-pole
Outer diameter	15,75 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.5 mm <sup>2</sup>		

**Electrical Data**

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Operating voltage	≤ 250 V DC ≤ 250 V AC
Permissible current strength per path, max.	1 A	Rated voltage	≤ 250 Vdc ≤ 250 Vac
Resistance	≤ 39 mΩ/m	Total current, max.	7 A

**Classifications**

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

**Environmental Product Compliance**

REACH SVHC /

**Downloads**Catalogues [Catalogues in PDF-format](#)