

**CC-M 43/70 AL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 43 x 70 mm, silver
Order No.	<a href="#">1500200000</a>
Type	CC-M 43/70 AL
GTIN (EAN)	4050118308938
Qty.	80 pc(s).

**CC-M 43/70 AL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	43 mm	Height (inches)	1.693 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	3.963 g		

**Temperatures**

Operating temperature range	-55...130 °C
-----------------------------	--------------

**General data**

Colour	silver	
Material	Chrome coated aluminium (AL), Anodized aluminium	
Number of markers per combination	1 MetalliCard = Device markers	
Number of markers per packaging unit	Form of supply	MetalliCard
Operating temperature range	-55...130 °C	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Recommended industries	Energy, Process	
Size of labelling field	41.3 x 68.3 mm	
Width	70 mm	

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### CC-M 43/70 AL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



**CC-M 43/70 AL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Complementary products****General ordering data**

Type	DKB CC 43/70	Version
Order No.	<a href="#">1500340000</a>	MetalliCard, Adhesive strip, 43 x 70 mm, Transparent
GTIN (EAN)	4050118309041	
Qty.	100 pc(s).	
Type	PRIMER CC-M	
Order No.	<a href="#">2068020000</a>	
GTIN (EAN)	4050118416534	
Qty.	100 pc(s).	
Type	INLAY CC-M 43/70	
Order No.	<a href="#">1500300000</a>	
GTIN (EAN)	4050118309027	
Qty.	1 pc(s).	