

**IE-C5DS4VG0700A60A60-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |  |
|------------|--|
| Version    | System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 70 m |
| Order No.  | <a href="#">1522100700</a>   |
| Type       | IE-C5DS4VG0700A60A60-E   |
| GTIN (EAN) | 4050118329056  |
| Qty.       | 1 pc(s).   |

## IE-C5DS4VG0700A60A60-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |                |
|------------|---------|-----------------|----------------|
| Length     | 70 m    | Length (inches) | 2,755.906 inch |
| Net weight | 4,615 g |                 |                |

## Temperatures

|                          |                |                       |                |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature      | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -40 °C...80 °C |                       |                |

## Cable specific standards

|                              |                          |                               |   |
|------------------------------|--------------------------|-------------------------------|---|
| Standard, assembly           | UL-Style 21694           | Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) |
| Standard, shielding material | DIN EN 13602 Cu-ETP-A..B | Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |

## Standards

|                              |                          |                               |   |
|------------------------------|--------------------------|-------------------------------|---|
| Standard, assembly           | UL-Style 21694           | Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) |
| Standard, shielding material | DIN EN 13602 Cu-ETP-A..B | Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |

## Cable structure

|                              |   |                                       |   |
|------------------------------|---|---------------------------------------|---|
| Arrangement of wire cores    | Star-quad   | Colour sequence or wires - wire pairs | white, yellow, blue, orange             |
| Complete shielding           | Aluminium foil, Shielding braid made from copper wiring | Cross-section                         | 4*AWG 22/7 - 0.32 mm <sup>2</sup>       |
| Diameter of inner sheathing  | 4.05 mm   | Filler                                | As central element                      |
| Insulation                   | PE  | Insulation cross-section              | 1.5 mm                                  |
| Material sheath              | PVC   | Number of wires                       | 4                                       |
| Overlap of shielding braid   | 85 %  | Sheath diameter, max.                 | 6.7 mm                                  |
| Sheath diameter, min.        | 6.3 mm  | Sheathing colour                      | green (RAL 6018)                        |
| Sheathing material thickness | 0.9 mm  | Shielding                             | SF/UTP                                  |
| Shielding braid thickness    | 0.13 mm   | Standard designations                 | 2YY(ST)CY<br>2x2x0,75/1,5-100 LI VZN GN |
| Strands                      | 7   | Wire material                         | Stranded tin-plated copper wire         |

## Electrical properties of cable

|                                |   |                               |                     |
|--------------------------------|---|-------------------------------|---------------------|
| Category                       | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Characteristic impedance      | 100 ± 5 Ω at 100MHz |
| Loop resistance                | 120 Ω/km                                    | Operating voltage (UL rating) | 600 V               |
| Operating voltage, UL          | 600 V                                       | Signal propagation time       | 5.3 ns/m            |
| Test voltage: wire-wire-shield | 2000 V <sub>eff</sub> , 50 Hz, 1 min        | Transfer impedance            | 20 mΩ/m at 10 MHz   |

## Mechanical and material properties of cable

|                                |  |                                 |                      |
|--------------------------------|--|---------------------------------|----------------------|
| Abrasion resistance            | good                                     | Halogen                         | Yes                  |
| Min. bending radius, once only | 3.5 *diameter                            | Min. bending radius, repetitive | 7.5 x cable diameter |
| Resistance to spread of flame  | in accordance with IEC 60332-1 / UL 1685 |                                 |                      |

Creation date May 23, 2024 5:02:46 AM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

## IE-C5DS4VG0700A60A60-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Plug, left

Plug left

RJ45, IP20, male contact, straight, plug, Plastic, shielded

## Plug, right

Plug right

RJ45, IP20, male contact, straight, plug, Plastic, shielded

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ECLASS 9.0  | 27-06-03-08 | ECLASS 9.1  | 27-06-03-08 |
| ECLASS 10.0 | 27-06-03-08 | ECLASS 11.0 | 27-06-03-08 |
| ECLASS 12.0 | 27-06-03-08 | ECLASS 13.0 | 27-06-03-08 |

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

[PROFINET Manufacturer's Declaration](#)

User Documentation

[MAN IE GUIDE DE](#)[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)[PI PROFINET CABLING EN](#)

## IE-C5DS4VG0700A60A60-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Wiring

| RJ45 |        | RJ45 |
|------|--------|------|
| 1    | yellow | 1    |
| 2    | orange | 2    |
| 3    | white  | 3    |
| 6    | blue   | 6    |