

**KLIPPON CS K41-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

IEC EX



On-site control with Ex-certified Klippon® Control Station: small command and signalling devices.  
Approved operating and display elements in stainless steel, aluminium or polyester enclosures.  
You want to control and safeguard your work processes in hazardous areas. For on-site control - approved Klippon® enclosure solutions with control and display elements.

**General ordering data**

Version	Klippon Control Station (control and signalling device), Control / signalling device, KLIPPON K41 EX, Aluminium AlSi12, Key-operated switch, 1 NC contact, 1 NO contacts, -55 °C...+55 °C, IP54, IP66
Order No.	<a href="#">1537490000</a>
Type	KLIPPON CS K41-1
GTIN (EAN)	4050118341904
Qty.	1 pc(s).
Cable gland	<a href="#">1460050000</a>
Reference product	<a href="#">9526920000</a>

Creation date June 4, 2024 12:12:41 AM CEST

## KLIPPON CS K41-1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	81 mm	Depth (inches)	3.189 inch
Depth with add-on components	108 mm	Height	122 mm
Height (inches)	4.803 inch	Width	120 mm
Width (inches)	4.724 inch	Net weight	1,265 g

## Temperatures

Ambient temperature	-55 °C...+55 °C
---------------------	-----------------

## Certificate numbers enclosure

Certificate No. (ATEX)	TUEV14ATEX7606X	Certificate No. (IECEX)	IECEXITA14.0013X
Certificate no. Terminal Box (ATEX)	TÜV 14 ATEX 7606 X	Certificate no. Terminal Box (IECEX)	IECEX ITA 14.0013X
Certificate no. Terminal Box (INMETRO)	LMP 21.0019X		

## General information

1 Position in enclosure	Key-operated switch	Contact design	1 NC contact, 1 NO contacts
Operating voltage, max.	400 V	Operating current at 40°C ambient temperature, max.	1.5 mm <sup>2</sup> - T6 10 A, 1.5 mm <sup>2</sup> - T5 16 A, 2.5 mm <sup>2</sup> - T6 16 A
Operating current at 55°C ambient temperature, max.	1.5 mm <sup>2</sup> - T4 16 A, 1.5 mm <sup>2</sup> - T5 10 A, 2.5 mm <sup>2</sup> - T5 16 A	Actuators	Key-operated switch, 3 switching positions, I - O - II, (I + II), latching, Key retractable
Drill holes side B	1 x M20	Lid attachment	Torx®-20 slothead screws
Seal material of operating and display elements	EPDM	Enclosure seal material	Silicone (VMQ)
Torque for lid screws	2.5 Nm	Earth stud torque	2.5 Nm
External earth	M4 earthing studs, stainless steel	Internal earth	Earth terminal
Marking	II 2 G Ex d e IIC T* Gb, II 2 D Ex tb IIIC T*°C Db	Cable gland clamping area, max.	12 mm
Cable gland clamping area, min.	3 mm	Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>
Type of mounting	Wall mounting	Surface finish	Powder-coated
Impact resistance	7 joules in acc. with IEC60079-0	Temperature class	T4, T5, T6
Material	Aluminium AlSi12		

## Housing

Drill holes side B	1 x M20	Material	Aluminium AlSi12
--------------------	---------	----------	------------------

## Classifications

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ETIM 9.0	EC002503
ECLASS 9.0	27-18-05-02	ECLASS 9.1	27-18-05-90
ECLASS 10.0	27-18-05-02	ECLASS 11.0	27-18-05-02
ECLASS 12.0	27-18-05-02	ECLASS 13.0	27-18-05-02

**KLIPPON CS K41-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	9e4cab4e-239c-4e14-b9df-a0fee300d28a

**Approvals**

Approvals


**ATEX****Downloads**

Approval/Certificate/Document of Conformity	<a href="#">TUEV14ATEX7606X</a> <a href="#">IECEXITA14.0013X</a> <a href="#">INMETRO Certificado INMETRO - LMP 21.0019X KCS</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">PI KLIPPON CS EN</a>

**KLIPPON CS K41-1**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**


Klippon CS POK 122209 - 4 - Lz8marLeBmss	
Actuating and illuminating elements	
B: Button	
L: Illuminated button	
L: Lamp	
n: NO	
m: NC and NO	
e: NC	
g: Green	
r: Red	
e: Emergency Stop	
p: Push	
k: Key	
3: Positions of the switch	
Drilling design	
Dimensions	
Enclosure Range	
POK (Polyester)	
K (Aluminium)	
STB (Stainless Steel)	
Product Name	
Control Station	
Brand Name	
Klippon®	

**KLIPPON CS K41-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Klippon® K - Wall-mounted holder**

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

**General ordering data**

Type	KLIPPON K MF KIT 25	Version
Order No.	<a href="#">9527590000</a>	Klippon K (aluminium empty enclosure), Mounting foot, Fixing lugs,
GTIN (EAN)	4032248014071	Height: 70 mm, Width: 33.5 mm, Depth: 12 mm, Material: Stainless
Qty.	1 pc(s).	steel 1.4301, silver