

IE-C5DS4VG0020A60A60-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

| | |
|------------|---|
| Version | System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 2 m |
| Order No. | 1522100020 |
| Type | IE-C5DS4VG0020A60A60-E |
| GTIN (EAN) | 4050118333541 |
| Qty. | 1 pc(s). |

IE-C5DS4VG0020A60A60-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-------|-----------------|------------|
| Length | 2 m | Length (inches) | 78.74 inch |
| Net weight | 145 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -40 °C...80 °C | | |

Cable specific standards

| | | | |
|------------------------------|--------------------------|-------------------------------|---|
| Standard, assembly | UL-Style 21694 | Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) |
| Standard, shielding material | DIN EN 13602 Cu-ETP-A..B | Standard, wire material | DIN EN 13602 Cu-ETP-A |

Standards

| | | | |
|------------------------------|--------------------------|-------------------------------|---|
| Standard, assembly | UL-Style 21694 | Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) |
| Standard, shielding material | DIN EN 13602 Cu-ETP-A..B | Standard, wire material | DIN EN 13602 Cu-ETP-A |

Cable structure

| | | | |
|------------------------------|---|---------------------------------------|---|
| Arrangement of wire cores | Star-quad | Colour sequence or wires - wire pairs | white, yellow, blue, orange |
| Complete shielding | Aluminium foil, Shielding braid made from copper wiring | Cross-section | 4*AWG 22/7 - 0.32 mm ² |
| Diameter of inner sheathing | 4.05 mm | Filler | As central element |
| Insulation | PE | Insulation cross-section | 1.5 mm |
| Material sheath | PVC | Number of wires | 4 |
| Overlap of shielding braid | 85 % | Sheath diameter, max. | 6.7 mm |
| Sheath diameter, min. | 6.3 mm | Sheathing colour | green (RAL 6018) |
| Sheathing material thickness | 0.9 mm | Shielding | SF/UTP |
| Shielding braid thickness | 0.13 mm | Standard designations | 2YY(ST)CY 2x2x0,75/1,5-100 LI VZN GN |
| Strands | 7 | Wire material | Stranded tin-plated copper wire |

Electrical properties of cable

| | | | |
|--------------------------------|---|-------------------------------|---------------------|
| Category | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Characteristic impedance | 100 ± 5 Ω at 100MHz |
| Loop resistance | 120 Ω/km | Operating voltage (UL rating) | 600 V |
| Operating voltage, UL | 600 V | Signal propagation time | 5.3 ns/m |
| Test voltage: wire-wire-shield | 2000 V _{eff} , 50 Hz, 1 min | Transfer impedance | 20 mΩ/m at 10 MHz |

Mechanical and material properties of cable

| | | | |
|--------------------------------|--|---------------------------------|----------------------|
| Abrasion resistance | good | Halogen | Yes |
| Min. bending radius, once only | 3.5 *diameter | Min. bending radius, repetitive | 7.5 x cable diameter |
| Resistance to spread of flame | in accordance with IEC 60332-1 / UL 1685 | | |

Creation date July 25, 2024 11:00:40 PM CEST

Catalogue status 13.07.2024 / We reserve the right to make technical changes.

IE-C5DS4VG0020A60A60-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Plug, left

Plug left

RJ45, IP20, male contact, straight, plug, Plastic, shielded

Plug, right

Plug right

RJ45, IP20, male contact, straight, plug, Plastic, shielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002599 | ETIM 7.0 | EC002599 |
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ECLASS 9.0 | 27-06-03-08 | ECLASS 9.1 | 27-06-03-08 |
| ECLASS 10.0 | 27-06-03-08 | ECLASS 11.0 | 27-06-03-08 |
| ECLASS 12.0 | 27-06-03-08 | ECLASS 13.0 | 27-06-03-08 |

Environmental Product Compliance

REACH SVHC

/

RoHS Compliance Status

Compliant without exemption

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[PROFINET Manufacturer's Declaration](#)

User Documentation

[MAN IE GUIDE DE](#)
[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)
[PI PROFINET CABLING EN](#)
[PI PROFINET CABLING EN](#)

IE-C5DS4VG0020A60A60-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Wiring

| RJ45 | | RJ45 |
|------|--------|------|
| 1 | yellow | 1 |
| 2 | orange | 2 |
| 3 | white | 3 |
| 6 | blue | 6 |