

MK 3/8 B 1-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Multi-pole terminal strips are suitable for wiring in junction boxes and small distribution boxes. The different numbers of poles offer the possibilities of direct mounting inside the housings.

General ordering data

| | |
|------------|---|
| Version | Single- and multi-pole terminal strip, Screw connection, 2.5 mm ² , 400 V, Number of poles: 8, 74.75 mm, medium yellow |
| Order No. | 1548120000 |
| Type | MK 3/8 B 1-6 |
| GTIN (EAN) | 4050118353846 |
| Qty. | 25 pc(s). |

MK 3/8 B 1-6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 16.1 mm | Depth (inches) | 0.634 inch |
| Height | 16.1 mm | Height (inches) | 0.634 inch |
| Width | 74.75 mm | Width (inches) | 2.943 inch |
| Net weight | 30 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | |
|--------|---------------|
| Colour | medium yellow |
|--------|---------------|

System specifications

| | |
|--------------------------|----|
| End cover plate required | No |
|--------------------------|----|

Additional technical data

| | |
|--------------------------|----|
| Explosion-tested version | No |
|--------------------------|----|

Conductors for clamping (additional connection)

| | |
|--|------------------|
| Connection type, additional connection | Screw connection |
|--|------------------|

Conductors for clamping (rated connection)

| | |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

General

| | |
|-----------------|---|
| Number of poles | 8 |
|-----------------|---|

Rating data

| | | | |
|---|---------------------|--|---------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 400 V |
| Rated DC voltage | 400 V | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Power loss in accordance with IEC 60947-7-x | 0.77 W | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001284 | ETIM 7.0 | EC001284 |
| ETIM 8.0 | EC001284 | ETIM 9.0 | EC001284 |
| ECLASS 9.0 | 27-14-11-06 | ECLASS 9.1 | 27-14-11-06 |
| ECLASS 10.0 | 27-14-11-06 | ECLASS 11.0 | 27-14-11-06 |
| ECLASS 12.0 | 27-14-11-06 | ECLASS 13.0 | 27-14-11-06 |

MK 3/8 B 1-6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Con-
formity

[UKCA declaration of conformity](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)