

CAN SUB-D SK TERM PS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Version	SUB-D
Order No.	1550590000
Type	CAN SUB-D SK TERM PS
GTIN (EAN)	4050118357134
Qty.	1 pc(s).

CAN SUB-D SK TERM PS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	17 mm	Depth (inches)	0.669 inch
Height	54 mm	Height (inches)	2.126 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	97 g		

Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

Technical specifications for sub-D connector

BUS PG interface	D-Sub 9-pole, Pin	BUS interface	D-Sub 9-pole, Pin
BUS, cable interface	Screw connection	Data rate	1 Mbps
Housing main material	ZnAl	Humidity	Max. 75% at +25°C, non-condensing
Interlock	UNC4-40	Outgoing elbow	90°
Plugging cycles	≥ 200	Programming interface	Yes
Protection degree	IP30	Temperature range of housing	-20...+70 ° C
Terminating resistor available	Yes		

Classifications

ETIM 6.0	EC001132	ETIM 7.0	EC001132
ETIM 8.0	EC001132	ETIM 9.0	EC001132
ECLASS 9.0	27-44-03-02	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-03-02	ECLASS 11.0	27-44-03-02
ECLASS 12.0	27-44-03-02	ECLASS 13.0	27-44-03-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcfaaf625

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN