

**KSW 4 8/5,08 1-8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

KSW marking strips are used to identify multi-pole PCB plug-in connectors. Users can print them individually without being confined to a certain pitch.

- Smudge-proof labelling
- Strips 2.5 mm and 4 mm wide
- Simply stick on - finished
- Optimum adhesion
- PVC-free

**General ordering data**

|            |   |
|------------|---|
| Version    | KSW, Terminal marker, 4 x 40.6 mm, Pitch in mm (P): 5.08 Weidmueller, white |
| Order No.  | <a href="#">1630200001</a>  |
| Type       | KSW 4 8/5,08 1-8  |
| GTIN (EAN) | 4008190246266   |
| Qty.       | 10 pc(s).   |

**KSW 4 8/5,08 1-8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Height     | 4 mm    | Height (inches) | 0.157 inch |
| Width      | 40.6 mm | Width (inches)  | 1.598 inch |
| Net weight | 0.7 g   |                 |            |

**Temperatures**

|                             |        |
|-----------------------------|--------|
| Operating temperature range | 150 °C |
|-----------------------------|--------|

**General data**

|                                   |                     |  |             |
|-----------------------------------|---------------------|--|-------------|
| Adhesive                          | Acrylate            | Application/manufacturer                     | Weidmueller |
| Colour                            | white               | Colour of printing                           | black       |
| Material                          | Polyester, PVC-free | Material colour according to resistance code | 9           |
| Number per sheet                  | 20                  | Operating temperature range                  | 150 °C      |
| Operating temperature range, max. | 150 °C              | Orientation of print                         | horizontal  |
| Printed characters                | Numbers             | Printing                                     | 1 - 8       |
| Printing method                   | Thermal transfer    | Type of printing                             | Standard    |
| Version                           | Self-adhesive       | Width  | 40.6 mm     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000761    | ETIM 7.0    | EC000761    |
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ECLASS 9.0  | 27-14-11-37 | ECLASS 9.1  | 27-14-11-37 |
| ECLASS 10.0 | 27-14-11-37 | ECLASS 11.0 | 27-28-11-01 |
| ECLASS 12.0 | 27-28-11-01 | ECLASS 13.0 | 27-28-11-01 |
| ECLASS 14.0 | 27-28-11-01 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
| Brochures  |  |