


**ZDU 2.5/4AN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |  |
|------------|--|
| Version    | Feed-through terminal, Tension-clamp connection, 2.5 mm <sup>2</sup> , 800 V, 24 A, dark beige |
| Order No.  | <a href="#">1608570000</a>   |
| Type       | ZDU 2.5/4AN  |
| GTIN (EAN) | 4008190077136  |
| Qty.       | 100 pc(s).   |

**ZDU 2.5/4AN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 38.5 mm    | Depth (inches) | 1.516 inch |
| Depth including DIN rail | 39.5 mm    | Height         | 79.5 mm    |
| Height (inches)          | 3.13 inch  | Width          | 5.1 mm     |
| Width (inches)           | 0.201 inch | Net weight     | 11.59 g    |

**Temperatures**

|                                  |                |                                  |   |
|----------------------------------|----------------|----------------------------------|---|
| Storage temperature              |                | Operating temperature range      | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
|                                  | -25 °C...55 °C |                                  |   |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C  |

**Material data**

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

**Rating data IECEx/ATEX**

|                                |   |                                 |                   |
|--------------------------------|---|---------------------------------|-------------------|
| Certificate No. (ATEX)         | DEMKO15ATEX1467U  | Certificate No. (IECEX)         | IECEXULD15.0008U  |
| Max. voltage (ATEX)            | 550 V   | Current (ATEX)                  | 22 A              |
| Wire cross section max. (ATEX) | 4 mm <sup>2</sup>   | Max. voltage (IECEX)            | 550 V             |
| Current (IECEX)                | 22 A  | Wire cross section max. (IECEX) | 4 mm <sup>2</sup> |
| Operating temperature range    | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7              |                   |
| Ex 2014/34/EU label            | II 2 G D  |                                 | Ex eb II C Gb     |

**System specifications**

|                               |  |                                     |       |
|-------------------------------|--|-------------------------------------|-------|
| Version                       | Tension-clamp connection, for plug-in cross-connector, One end without connector | End cover plate required            | Yes   |
| Number of levels              | 1  | Number of clamping points per level | 4     |
| Number of potentials per tier | 1  | Levels cross-connected internally   | No    |
| PE connection                 | No   | Rail                                | TS 35 |

**Additional technical data**

|                             |         |                     |        |
|-----------------------------|---------|---------------------|--------|
| Explosion-tested version    | Yes     | Installation advice | Busbar |
| Number of similar terminals | 1       | Open sides          | right  |
| Type of mounting            | Snap-on |                     |        |

**CSA rating data**

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1152892 | Current size B (CSA)          | 27 A   |
| Current size C (CSA)          | 27 A           | Current size D (CSA)          | 5 A    |
| Voltage size B (CSA)          | 600 V          | Voltage size C (CSA)          | 600 V  |
| Voltage size D (CSA)          | 600 V          | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

**ZDU 2.5/4AN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Conductors for clamping (additional connection)**

Connection type, additional connection Tension-clamp connection

**Conductors for clamping (rated connection)**

|   |                      |   |                          |
|---|----------------------|---|--------------------------|
| Blade size  | 0.6 x 3.5 mm         | Clamping range, max.  | 4 mm <sup>2</sup>        |
| Clamping range, min.  | 0.05 mm <sup>2</sup> | Connection direction  | top                      |
| Gauge to IEC 60947-1  | A3                   | Number of connections   | 4                        |
| Stripping length  | 10 mm                | Type of connection  | Tension-clamp connection |
| Wire connection cross section AWG, max.   | AWG 12               | Wire connection cross section AWG, min.   | AWG 30                   |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>      |
| Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup>      |

**General**

|   |               |   |        |
|---|---------------|---|--------|
| Installation advice                     | Busbar        | Rail                                    | TS 35  |
| Standards                               | IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 12 |
| Wire connection cross section AWG, min. | AWG 30        |   |        |

**Rating data**

|  |                     |                                 |               |
|--|---------------------|---------------------------------|---------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 800 V         |
| Rated DC voltage                             | 800 V               | Rated current                   | 24 A          |
| Current at maximum wires                     | 27 A                | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 8 kV          |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Pollution severity              | 3             |

**UL rating data**

Certificate No. (cURus) E60693

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ECLASS 9.0  | 27-14-11-20 | ECLASS 9.1  | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-01 |

## ZDU 2.5/4AN

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                           |            |
|---------------------------|------------|
| ROHS                      | Conform    |
| UL File Number Search     | UL Website |
| Certificate No. (cURus)   | E60693     |
| Certificate No. (cURusEX) | E184763    |

## Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">UKCA Ex Attestation of Conformity</a><br><a href="#">IECEX Certificate</a><br><a href="#">CB Test Certificate</a><br><a href="#">CB Certificate</a><br><a href="#">DNVGL certificate</a><br><a href="#">Lloyds Register Certificate</a><br><a href="#">CCC Ex Certificate</a><br><a href="#">ATEX Certificate</a><br><a href="#">UKCA Ex Certificate</a><br><a href="#">RINA Certificate</a><br><a href="#">Declaration of Conformity</a><br><a href="#">UKCA declaration of conformity</a><br><a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Engineering Data                            | <a href="#">Zuken E3.S</a>   |
| Product Change Notification                 | <a href="#">PCN ZDU 2.5 4AN DE</a><br><a href="#">PCN ZDU 2.5 4AN EN</a>   |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">NTI ZDU/ZPE 2.5/4AN</a><br><a href="#">User Manual Z-Series</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   |  |

### ZDU 2.5/4AN

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

