

WO 76/25 TP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	WriteOn, Conductor and cable markers, 6 - 18 mm, 25.4 x 76 mm, white
Order No.	1609760000
Type	WO 76/25 TP
GTIN (EAN)	4008190008789
Qty.	1 pc(s).

WO 76/25 TP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	25.4 mm	Height (inches)	1 inch
Width	76 mm	Width (inches)	2.992 inch
Net weight	39 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Material	Vinyl film	Material colour according to resistance code	9
Number per sheet	60	Operating temperature range	-40...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Type of printing	neutral	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	76 mm

Conductor and cable markers

Conductor O.D.	6 - 18 mm	Conductor O.D., max.	18 mm
Conductor O.D., min.	6 mm	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 70 mm ²
Halogen	Yes	Text field height	25.4 mm
Text field width	19.05 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Important note

Product information	1 BAGPACK = 60 PIECES
---------------------	-----------------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Catalogues	Catalogues in PDF-format