

ZQS 2.5/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Accessories, Cross-connector, 24 A
Order No.	1633230000
Type	ZQS 2.5/5
GTIN (EAN)	4008190263416
Qty.	20 pc(s).

ZQS 2.5/5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	31.6 mm	Depth (inches)	1.244 inch
Height	53.2 mm	Height (inches)	2.094 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	7.1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	120		

Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

Cross-connector

Number of cross-connected terminals	5	Rated current, multi-pole	10 A
Type	Cross-connector		

Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	5
---------------------	-----------------	-----------------	---

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

ZQS 2.5/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Important note**

Product information

Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used

Approvals

ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[Confirmation of Standards EN 45545-2_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures