


**SLS 5.08/03/180B SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

**General ordering data**

|              |   |
|--------------|---|
| Version      | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 3, 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², Box |
| Order No.    | <a href="#">1645240000</a>  |
| Type         | SLS 5.08/03/180B SN BK BX   |
| GTIN (EAN)   | 4008190284459   |
| Qty.         | 108 pc(s).  |
| Product data | IEC: 400 V / 21.5 A / 0.2 - 2.5 mm²<br>UL: 300 V / 14 A / AWG 26 - AWG 12   |
| Packaging    | Box   |

Creation date July 14, 2024 8:56:28 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

## SLS 5.08/03/180B SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 22.2 mm | Depth (inches)  | 0.874 inch |
| Height     | 15.3 mm | Height (inches) | 0.602 inch |
| Net weight | 4.93 g  |                 |            |

## System Parameters

|  |  |                   |                            |
|--|--|-------------------|----------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 5.08              |                   |                            |
| Type of connection                           | Field connection                                 |                   |                            |
| Wire connection method                       | Clamping yoke connection                         |                   |                            |
| Pitch in mm (P)                              | 5.08 mm  |                   |                            |
| Pitch in inches (P)                          | 0.2 "  |                   |                            |
| Conductor outlet direction                   | 180°   |                   |                            |
| Number of poles                              | 3  |                   |                            |
| L1 in mm                                     | 10.16 mm   |                   |                            |
| L1 in inches                                 | 0.4 "  |                   |                            |
| Number of rows                               | 1  |                   |                            |
| Pin series quantity                          | 1  |                   |                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe plugged/ back-of-hand-safe unplugged |                   |                            |
| Touch-safe protection acc. to DIN VDE 0470   | IP20 plugged/ IP10 unplugged                     |                   |                            |
| Protection degree                            | IP20, when fully mounted                         |                   |                            |
| Volume resistance                            | ≤5 mΩ  |                   |                            |
| Can be coded                                 | Yes  |                   |                            |
| Stripping length                             | 7 mm   |                   |                            |
| Clamping screw                               | M 2.5  |                   |                            |
| Screwdriver blade                            | 0.6 x 3.5  |                   |                            |
| Screwdriver blade standard                   | DIN 5264-A                                       |                   |                            |
| Plugging cycles                              | 25   |                   |                            |
| Plugging force/pole, max.                    | 4 N  |                   |                            |
| Pulling force/pole, max.                     | 3 N  |                   |                            |
| Tightening torque                            | Torque type                                      | Wire connection   |                            |
|  | Usage information                                | Tightening torque | min. 0.4 Nm<br>max. 0.5 Nm |

## Material data

|                                       |          |                                       |                            |
|---------------------------------------|----------|---------------------------------------|----------------------------|
| Insulating material                   | PBT      | Colour                                | black                      |
| Colour chart (similar)                | RAL 9011 | Insulating material group             | IIIa                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Insulation strength                   | ≥ 10 <sup>8</sup> Ω        |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-alloy                   |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 µm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C                     |

## Conductors suitable for connection

|   |                      |
|---|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 3.31 mm <sup>2</sup> |
| Wire connection cross section AWG, min. | AWG 26               |
| Wire connection cross section AWG, max. | AWG 12               |
| Solid, min. H05(07) V-U                 | 0.2 mm <sup>2</sup>  |

Creation date July 14, 2024 8:56:28 AM CEST

## SLS 5.08/03/180B SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |  |                              |                        |      |
|---|--|------------------------------|------------------------|------|
| Solid, max. H05(07) V-U   | 2.5 mm <sup>2</sup>  |                              |                        |      |
| Stranded, min. H07V-R   | 0.2 mm <sup>2</sup>  |                              |                        |      |
| Stranded, max. H07V-R   | 2.5 mm <sup>2</sup>  |                              |                        |      |
| Flexible, min. H05(07) V-K  | 0.2 mm <sup>2</sup>  |                              |                        |      |
| Flexible, max. H05(07) V-K  | 2.5 mm <sup>2</sup>  |                              |                        |      |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |  |                              |                        |      |
| w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm <sup>2</sup> max. |  |                              |                        |      |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>  |                              |                        |      |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 2.5 mm <sup>2</sup>  |                              |                        |      |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.8 mm x 2.0 mm; 2.4 mm  |                              |                        |      |
| Clampable conductor   | Cross-section for conductor connection   | Type                         | fine-wired             |      |
|   |  | nominal                      | 0.5 mm <sup>2</sup>    |      |
|   | wire end ferrule   | Stripping length             | nominal                | 6 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H0.5/6</a> |      |
|   | Cross-section for conductor connection   | Type                         | fine-wired             |      |
|   |  | nominal                      | 1 mm <sup>2</sup>      |      |
|   | wire end ferrule   | Stripping length             | nominal                | 6 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H1.0/6</a> |      |
|   | Cross-section for conductor connection   | Type                         | fine-wired             |      |
|   |  | nominal                      | 1.5 mm <sup>2</sup>    |      |
|   | wire end ferrule   | Stripping length             | nominal                | 7 mm |
|   |  | Recommended wire-end ferrule | <a href="#">H1.5/7</a> |      |
| Cross-section for conductor connection                              | Type   | fine-wired                   |                        |      |
|   | nominal  | 2.5 mm <sup>2</sup>          |                        |      |
| wire end ferrule  | Stripping length   | nominal                      | 7 mm                   |      |
|   | Recommended wire-end ferrule   | <a href="#">H2.5/7</a>       |                        |      |
| Cross-section for conductor connection                              | Type   | fine-wired                   |                        |      |
|   | nominal  | 0.75 mm <sup>2</sup>         |                        |      |
| wire end ferrule  | Stripping length   | nominal                      | 6 mm                   |      |
|   | Recommended wire-end ferrule   | <a href="#">H0.75/6</a>      |                        |      |
| Reference text  | The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage. |                              |                        |      |

## Rated data acc. to IEC

|   |                        |   |                   |
|---|------------------------|---|-------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 21.5 A            |
| Rated current, max. number of poles (Tu=20°C)                             | 16 A                   | Rated current, min. number of poles (Tu=40°C)                         | 18 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 14 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 400 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## SLS 5.08/03/180B SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

200039-1121690

|                                   |  |
|-----------------------------------|--|
| Rated voltage (Use group B / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 15 A   |
| Wire cross-section, AWG, min.     | AWG 26   |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |        |
|-----------------------------------|--------|
| Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, max.     | AWG 12 |

## Rated data acc. to UL 1059

Institute (UR)



Certificate No. (UR)

E60693

|                                       |  |
|---------------------------------------|--|
| Rated voltage (Use group B / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 14 A   |
| Wire cross-section, AWG, min.         | AWG 26   |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |

|                                       |        |
|---------------------------------------|--------|
| Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, max.         | AWG 12 |

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 349 mm |
| VPE width | 137 mm | VPE height | 31 mm  |

## Type tests

|                               |                |   |
|-------------------------------|----------------|---|
| Test: Durability of markings  | Standard       | VDE 0627 Tab. 7 item 3/6.86                             |
|                               | Test           | durability  |
|                               | Evaluation     | passed  |
| Test: Clampable cross section | Standard       | VDE 0609 part 1 06.83, EN 60947-1 03.91                 |
|                               | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section |
|                               |                | Type of conductor and H05V-K0.5 conductor cross-section |
|                               |                | Type of conductor and H05V-U2.5 conductor cross-section |
|                               |                | Type of conductor and H05V-K2.5 conductor cross-section |
|                               |                | Type of conductor and AWG 28 conductor cross-section    |
|                               |                | Type of conductor and AWG 14 conductor cross-section    |
|                               | Evaluation     | passed  |

## SLS 5.08/03/180B SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |                |   |
|---|----------------|---|
| Test for damage to and accidental loosening of conductors | Standard       | EN 60947-1/1991 section 8.2.4.3                         |
|   | Requirement    | 0.3 kg  |
|   | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section |
|   |                | Type of conductor and H05V-K0.5 conductor cross-section |
|   | Evaluation     | passed  |
|   | Requirement    | 0.7 kg  |
|   | Conductor type | Type of conductor and H07V-U2.5 conductor cross-section |
|   |                | Type of conductor and H07V-K2.5 conductor cross-section |
|   | Evaluation     | passed  |
| Pull-out test   | Standard       | EN 60947-1/1991 section 8.2.4.4                         |
|   | Requirement    | ≥5 N  |
|   | Conductor type | Type of conductor and AWG 28/1 conductor cross-section  |
|   |                | Type of conductor and AWG 28/7 conductor cross-section  |
|   | Evaluation     | passed  |
|   | Requirement    | ≥50 N   |
|   | Conductor type | Type of conductor and H07V-U2.5 conductor cross-section |
|   |                | Type of conductor and H07V-K2.5 conductor cross-section |
|   |                | Type of conductor and AWG 14/19 conductor cross-section |
|   | Evaluation     | passed  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ECLASS 9.0  | 27-44-03-09 | ECLASS 9.1  | 27-44-03-09 |
| ECLASS 10.0 | 27-44-03-09 | ECLASS 11.0 | 27-46-02-02 |
| ECLASS 12.0 | 27-46-02-02 | ECLASS 13.0 | 27-46-02-02 |

## Environmental Product Compliance

REACH SVHC

/

**SLS 5.08/03/180B SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Important note**

|                |   |
|----------------|---|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.  |
| Notes          | <ul style="list-style-type: none"><li>• Additional variants on request</li><li>• Rated current related to rated cross-section &amp; min. No. of poles.</li><li>• Wire end ferrule without plastic collar to DIN 46228/1</li><li>• Wire end ferrule with plastic collar to DIN 46228/4</li><li>• P on drawing = pitch</li><li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li><li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li><li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li></ul> |

**Approvals**

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E60693     |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>                              |
| Catalogues       | <a href="#">Catalogues in PDF-format</a>                     |
| Brochures        | <a href="#">FL DRIVES EN</a><br><a href="#">FL DRIVES DE</a> |


## SLS 5.08/03/180B SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Product image



### Dimensional drawing



### Graph



### Graph



### Graph



### Product benefits



Lower assembly costs  
Secure in a matter of seconds

### SLS 5.08/03/180B SN BK BX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Product benefits



Flexible application options  
For 3 connection systems




WEIDMÜLLER INTERFAC GmbH & Co.KG  
WEITERGABE SOWIE VERVIELFÄLTIGUNG DIESER DOKUMENTS, VERWERTUNG UND MITTEILUNG SEINER INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRUECKLICH GESTATET.  
ZUWIDERHANDLUNGEN VERPFLICHTEN ZU SCHADENERSATZ. ALLE RECHTE FUER DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTERREINTRAGUNG VORBEHALTEN.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMUELLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.

MASS E OHNE TOLERANZ SIND KEINE PRUEFMASS E  
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.


ALLGEMEINGUELTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE  
GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED

DIE DEUTSCHE VERSION IST VERBINDLICH  
THE GERMAN VERSION IS BINDING


SHOWN: SLS 5.08/04/180




SCREWDRIVER



CONDUCTOR




SHOWN: SLS 5.08/04/180B



SCREWDRIVER






CONDUCTOR



For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.


Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

SHOWN: SLS 5.08/04/180DF



|                                  |                                    |        |          |
|----------------------------------|------------------------------------|--------|----------|
| 0.5-0.8                          | 0.019-0.031                        | 6.3    | 0.248    |
| 1.00                             | 0.039                              | 6.4    | 0.252    |
| 1.5                              | 0.059                              | 6.5    | 0.256    |
| 2.00                             | 0.079                              | 6.7    | 0.264    |
| WANDDICKE<br>WALL THICKNESS [mm] | WANDDICKE<br>WALL THICKNESS [inch] | d [mm] | d [inch] |

SCREWDRIVER



CONDUCTOR

P=5.08 RASTER PITCH

|                    |         |           |
|--------------------|---------|-----------|
| 24                 | 106.84  | 4.600     |
| 23                 | 111.76  | 4.400     |
| 22                 | 106.68  | 4.200     |
| 21                 | 101.60  | 4.000     |
| 20                 | 96.52   | 3.800     |
| 19                 | 91.44   | 3.600     |
| 18                 | 86.36   | 3.400     |
| 17                 | 81.28   | 3.200     |
| 16                 | 76.20   | 3.000     |
| 15                 | 71.12   | 2.800     |
| 14                 | 66.04   | 2.600     |
| 13                 | 60.96   | 2.400     |
| 12                 | 55.88   | 2.200     |
| 11                 | 50.80   | 2.000     |
| 10                 | 45.72   | 1.800     |
| 9                  | 40.64   | 1.600     |
| 8                  | 35.56   | 1.400     |
| 7                  | 30.48   | 1.200     |
| 6                  | 25.40   | 1.000     |
| 5                  | 20.32   | 0.800     |
| 4                  | 15.24   | 0.600     |
| 3                  | 10.16   | 0.400     |
| 2                  | 5.08    | 0.200     |
| n POLZAHL<br>POLES | L1 [mm] | L1 [inch] |

METRIC TOLERANCES  
X. = ±0.3  
X.X = ±0.1  
X.XX = ±0.05

70327/5  
22.05.13 HELIS\_MA

01

MODIFICATION

SCALE: 2/1  
SUPERSEDES: .

DATE

27.08.2003

27.05.2013

NAME

#AttributeError: Benutzer None nicht gefunden.

HECKERT\_M

HECKERT\_M

PRODUCT FILE: SLS 5.08

7314

CAT.NO.: .

**C 21277** 18

DRAWING NO. SHEET 01 OF 01 SHEETS

ISSUE NO.

**Weidmüller**

**SLS 5.08/./180...**  
STIFTSTECKER  
MALE PLUG