

**VT SF 3/21 MC NE BL V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

**Advantages:**

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

Version	SlimFix, Conductor and cable markers, 3 - 3.7 mm, 21 x 4.6 mm, blue
Order No.	<a href="#">1689430002</a>
Type	VT SF 3/21 MC NE BL V0
GTIN (EAN)	4008190872489
Qty.	512 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

## VT SF 3/21 MC NE BL V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	21 mm	Height (inches)	0.827 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	0.42 g		

## Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

## General data

Colour	blue
Halogen	No
Material	Polyamide 66
Number of markers per combination	1 MultiCard = Conductor and cable markers
Number of markers per packaging unit	Form of supply MultiCard
Operating temperature range	-50...120 °C
Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C
Recommended industries	Transportation, Machinery
Size of labelling field	21 x 4.6 mm
Type of printing	neutral
UL 94 flammability rating	V-0
Width	4.6 mm

## Conductor and cable markers

Conductor O.D.	3 - 3.7 mm	Conductor O.D., max.	3.7 mm
Conductor O.D., min.	3 mm	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Cross-section for connected wire	1.5 - 2.5 mm <sup>2</sup>
Halogen	No		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**VT SF 3/21 MC NE BL V0**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

