


**VT SFX 14/23 MC NE GE V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | SlimFix X, Conductor and cable markers, 7 - 40 mm, 23 x 14 mm, yellow            |
| Order No.          | <a href="#">1689490004</a>   |
| Type               | VT SFX 14/23 MC NE GE V0   |
| GTIN (EAN)         | 4008190872656  |
| Qty.               | 320 pc(s).   |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

## VT SFX 14/23 MC NE GE V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.5 mm  | Depth (inches)  | 0.02 inch  |
| Height     | 23 mm   | Height (inches) | 0.906 inch |
| Width      | 14 mm   | Width (inches)  | 0.551 inch |
| Net weight | 0.641 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -50...120 °C |
|-----------------------------|--------------|

## General data

|  |   |
|--|---|
| Colour                                       | yellow                                    |
| Halogen                                      | No  |
| Material                                     | Polyamide 66                              |
| Material colour according to resistance code | 4   |
| Number of markers per combination            | 1 MultiCard = Conductor and cable markers |
| Number of markers per packaging unit         | Form of supply MultiCard                  |
| Operating temperature range                  | -50...120 °C                              |
| Operating temperature range, max.            | 120 °C                                    |
| Operating temperature range, min.            | -50 °C                                    |
| Recommended industries                       | Transportation, Machinery                 |
| Size of labelling field                      | 23 x 8 mm                                 |
| Type of printing                             | neutral                                   |
| UL 94 flammability rating                    | V-0                                       |
| Version                                      | Installation with cable ties              |
| Width  | 14 mm                                     |

## Conductor and cable markers

|                               |                    |                                  |                          |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 7 - 40 mm          | Conductor O.D., max.             | 40 mm                    |
| Conductor O.D., min.          | 7 mm               | Conductor cross-section, max.    | 500 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |
| Halogen                       | No                 |                                  |                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### VT SFX 14/23 MC NE GE V0

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

**VT SFX 14/23 MC NE GE V0**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

