

KLBU 4-13.5 SC M4X16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

General ordering data

| | |
|------------|-------------------------------------|
| Version | Clamping yoke, Clamping yoke, Steel |
| Order No. | 1712311002 |
| Type | KLBU 4-13.5 SC M4X16 |
| GTIN (EAN) | 4032248064403 |
| Qty. | 10 pc(s). |

KLBUE 4-13.5 SC M4X16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Depth | 31.45 mm | Depth (inches) | 1.238 inch |
| Height | 22 mm | Height (inches) | 0.866 inch |
| Width | 20.1 mm | Width (inches) | 0.791 inch |
| Net weight | 19.2 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|-------|--------|--------|
| Material | Steel | Colour | silver |
|----------|-------|--------|--------|

System specifications

| | |
|---------|-------------------------|
| Version | For a shield connection |
|---------|-------------------------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | Snap-on | Type of mounting | Screw |

Conductors for clamping (rated connection)

| | | | |
|----------------------|---------|----------------------|------|
| Cable diameter, max. | 13.5 mm | Cable diameter, min. | 4 mm |
|----------------------|---------|----------------------|------|

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 20 mm |
|-----------------|-------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002020 | ETIM 7.0 | EC002020 |
| ETIM 8.0 | EC002020 | ETIM 9.0 | EC002020 |
| ECLASS 9.0 | 27-14-11-50 | ECLASS 9.1 | 27-14-11-50 |
| ECLASS 10.0 | 27-14-11-50 | ECLASS 11.0 | 27-14-11-50 |
| ECLASS 12.0 | 27-14-11-50 | ECLASS 13.0 | 27-25-01-20 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

KLBUE 4-13.5 SC M4X16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |