

**LM WO 18/34 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

**General ordering data**

Version	LaserMark, Conductor and cable markers, 5 - 7 mm, 18 x 34 mm, white
Order No.	<a href="#">1695711044</a>
Type	LM WO 18/34 WS
GTIN (EAN)	4008190924652
Qty.	10 pc(s).

## LM WO 18/34 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	18 mm	Height (inches)	0.709 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	10.2 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Acrylate		
Colour	white		
Halogen	No		
Material	Polyester film		
Material colour according to resistance code	9		
Number of markers per combination	1 Label sheet = 88 Conductor and cable markers		
Number of markers per packaging unit	Number of markers per combination	88	
	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
Number of markers per packaging unit	880		
Number per sheet	88		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Size of labelling field	18 x 12.7 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	34 mm		

## Conductor and cable markers

Conductor O.D.	5 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	5 mm	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	6 mm <sup>2</sup>	Cross-section for connected wire	6 - 16 mm <sup>2</sup>
Halogen	No	Text field height	13 mm
Text field width	17.8 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

### LM WO 18/34 WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

