

BS 35II/KLBUE 4-13.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the TS 35 DIN rail. The shield is diverted from the shield clamping saddles via the mounting foot to the TS 35 mounting rail and thus to PE (ground).

General ordering data

| | |
|------------|--------------------------------------|
| Version | Clamping yoke, Set of fixings, Steel |
| Order No. | 1723820000 |
| Type | BS 35II/KLBUE 4-13.5 |
| GTIN (EAN) | 4008190377014 |
| Qty. | 10 pc(s). |

BS 35II/KLBUE 4-13.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|----------|---------|-----------------|------------|
| Depth | 36.5 mm | Depth (inches) | 1.437 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Diameter | 3 mm | Net weight | 68.961 g |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|-------|--------|--------|
| Material | Steel | Colour | silver |
|----------|-------|--------|--------|

System specifications

| | |
|---------|---------------|
| Version | Clamping yoke |
|---------|---------------|

Additional technical data

| | | | |
|--------------------------|-----|----------------|-----------------|
| Explosion-tested version | Yes | Type of fixing | when screwed in |
|--------------------------|-----|----------------|-----------------|

Conductors for clamping (rated connection)

| | | | |
|----------------------|---------|----------------------|------|
| Cable diameter, max. | 13.5 mm | Cable diameter, min. | 4 mm |
|----------------------|---------|----------------------|------|

Dimensions

| | |
|----------|------|
| Diameter | 3 mm |
|----------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ECLASS 9.0 | 27-14-11-92 | ECLASS 9.1 | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |