


VT SF 4/12 MC NE RT V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 3.6 - 6 mm, 12 x 5.7 mm, red
Order No.	1746030003
Type	VT SF 4/12 MC NE RT V0
GTIN (EAN)	4008190986377
Qty.	192 pc(s).
Alternative product	1919610000
compatible printer	2715590000 2438520000 2438510000

VT SF 4/12 MC NE RT V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.24 inch
Height	12 mm	Height (inches)	0.472 inch
Width	5.7 mm	Width (inches)	0.224 inch
Net weight	0.64 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

General data

Colour	red
Halogen	No
Material	Polyamide 66
Material colour according to resistance code	2
Number of markers per combination	1 MultiCard = Conductor and cable markers
Number of markers per packaging unit	Form of supply MultiCard
Operating temperature range	-50...120 °C
Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C
Recommended industries	Transportation, Machinery
Size of labelling field	12 x 5.7 mm
Type of printing	neutral
UL 94 flammability rating	V-0
Width	5.7 mm

Conductor and cable markers

Conductor O.D.	3.6 - 6 mm	Conductor O.D., max.	6 mm
Conductor O.D., min.	3.6 mm	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	2.5 mm ²	Cross-section for connected wire	2.5 - 4 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

VT SF 4/12 MC NE RT V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

VT SF 4/12 MC NE RT V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

