


ESG 9/17 K MC NE GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 17 mm, PA 66, Colour: yellow, Self-adhesive
Order No.	1753500000
Type	ESG 9/17 K MC NE GE
GTIN (EAN)	4032248010738
Qty.	200 pc(s).
compatible printer	2715590000 2438520000 2438510000

ESG 9/17 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	9 mm	Height (inches)	0.354 inch
Width	17 mm	Width (inches)	0.669 inch
Net weight	0.381 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

General data

Adhesive	Double-sided adhesive tape		
Application/manufacturer	Self-adhesive		
Colour	yellow		
Halogen	No		
Material	PA 66		
Material colour according to resistance code	4		
Number of markers per combination	1 MultiCard = Device markers		
Number of markers per packaging unit	Form of supply	MultiCard	
Number per sheet	40		
Operating temperature range	-40...60 °C		
Operating temperature range, max.	60 °C		
Operating temperature range, min.	-40 °C		
UL 94 flammability rating	V-2		
Version	Self-adhesive		
Width	17 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

ESG 9/17 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	MultiCard Material modification MultiCard Material Modifikation
Catalogues	Catalogues in PDF-format

ESG 9/17 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

