

**ZQV 4N/3 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

|                     |  |
|---------------------|--|
| Version             | W-Series, Cross-connector, 32 A                                |
| Order No.           | <a href="#">1762630000</a>                                     |
| Type                | ZQV 4N/3 GE  |
| GTIN (EAN)          | 4032248169788  |
| Qty.                | 60 pc(s).  |
| Delivery status     | <b>This article will no longer be available in the future.</b> |
| Available until     | 2021-12-31   |
| Alternative product | <a href="#">1527940000</a>                                     |

## ZQV 4N/3 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 25.7 mm | Depth (inches)  | 1.012 inch |
| Height     | 17 mm   | Height (inches) | 0.669 inch |
| Width      | 2.8 mm  | Width (inches)  | 0.11 inch  |
| Net weight | 1.95 g  |                 |            |

## Temperatures

|                                  |                |                                  |     |
|----------------------------------|----------------|----------------------------------|-----|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 |
| Continuous operating temp., max. | 130            |                                  |     |

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | yellow |
| UL 94 flammability rating | V-0   |        |        |

## System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

## Additional technical data

|                          |     |                |         |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

## Cross-connector

|                                     |      |                       |                 |
|-------------------------------------|------|-----------------------|-----------------|
| Number of cross-connected terminals | 3    | Rated current, 2-pole | 32 A            |
| Rated current, multi-pole           | 32 A | Type                  | Cross-connector |

## Dimensions

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 6.1 mm |
|-----------------|--------|

## General

|                 |   |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

## Rating data

|               |      |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

**ZQV 4N/3 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Important note**

## Product information

Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used

**Approvals**

ROHS

Conform

**Downloads**

Engineering Data

[CAD data – STEP](#)

Engineering Data

[Zuken E3.S](#)

User Documentation

[Storage Conditions](#)[Terminal Blocks](#)  
[User Manual ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures