

KLBUE 15-32 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1752711001
Type	KLBUE 15-32 CPF
GTIN (EAN)	4032248044443
Qty.	10 pc(s).

KLBUE 15-32 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	32 mm	Height (inches)	1.26 inch
Width	33.5 mm	Width (inches)	1.319 inch
Net weight	84.5 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	grey
----------	-------	--------	------

System specifications

Version	For a shield connection	Rail	TS 27
---------	-------------------------	------	-------

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	when screwed in		

Conductors for clamping (rated connection)

Cable diameter, max.	32 mm	Cable diameter, min.	15 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	36 mm
-----------------	-------

General

Installation advice	Direct mounting	Rail	TS 27
---------------------	-----------------	------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20
ECLASS 14.0	27-25-01-20		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

KLBUE 15-32 CPF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

KLBUE 15-32 CPF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 27X12.5M/ST/F.ZN	Version
Order No.	1802690000	Terminal rail, Terminal rails, Steel, galvanized, Width: 2000 mm,
GTIN (EAN)	4032248257201	Height: 27 mm, Depth: 12.5 mm, Slit width: 9.00 mm, Slit length:
Qty.	2 m	9.00 mm