

**THM WO 17.8/34 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 4.4 - 6.7 mm, 17.8 x 33.9 mm, white
Order No.	<a href="#">1774380000</a>
Type	THM WO 17.8/34 WS
GTIN (EAN)	4032248148561
Qty.	1 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

## THM WO 17.8/34 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	17.8 mm	Height (inches)	0.701 inch
Width	33.9 mm	Width (inches)	1.335 inch
Net weight	388 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Polyacrylate adhesive		
Approval acc. to UL 969	Yes		
Colour	white		
Halogen	No		
Material	Polyester film		
Material colour according to resistance code	9		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Number of markers per packaging unit	Form of supply	Label reel	
Number per roll	3,000		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Size of labelling field	13 x 17.8 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	33.9 mm		

## Conductor and cable markers

Conductor O.D.	4.4 - 6.7 mm	Conductor O.D., max.	6.7 mm
Conductor O.D., min.	4.4 mm	Conductor cross-section, max.	35 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Cross-section for connected wire	0.75 - 35 mm <sup>2</sup>
Halogen	No	Text field height	17.8 mm
Text field width	13 mm		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Technical data

### Approvals

ROHS

Conform

### Downloads


Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Drawings



**THM WO 17.8/34 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	RIBBON MM 110/360 SW	Version
Order No.	<a href="#">2005070000</a>	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	