

SAIBW-5/9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Version	Field attachable connector, M12, Socket, angled
Order No.	1807330000
Type	SAIBW-5/9
GTIN (EAN)	4032248278558
Qty.	1 pc(s).

SAIBW-5/9

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	28 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	4...6 mm (PG7)/ 6...8 mm (PG9)	Cable diameter, max.	8 mm
Cable diameter, min.	6 mm	Coding	A-coded
Conductor cross-section, max.	0.75 mm ²	Conductor cross-section, min.	0.14 mm ²
Connection cross-section, max.	0.75 mm ²	Connection cross-section, min.	0.14 mm ²
Contact surface	CuSnZn	Contact surface	CuSnZn (5-pole) / gold plated (8-pole)
Housing main material	PA	Insulation strength	10 ⁸ Ω
Number of poles	5	Plugging cycles	≥ 50
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	60 V
Shield connection	No	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Screw connection

General Info

Number of poles	5	Connection 1	M12
Connection 2	Screw	Description of article	SAISW / SAIBW
Housing main material	PA	Connection thread	M12
Contact surface	CuSnZn	Protection degree	IP67
Plugging cycles	≥ 50		

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Imidazolidine-2-thione 96-45-7
SCIP	bcee35cf-c0f5-43d2-8daf-65ab0d08641a

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

SAIBW-5/9

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAIBW-5/9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

