

**TS 27X12.5M/ST/F.ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

**General ordering data**

|            |   |
|------------|---|
| Version    | Terminal rails, Rail, DIN EN 60715, Steel |
| Order No.  | <a href="#">1802690000</a>                |
| Type       | TS 27X12.5M/ST/F.ZN                       |
| GTIN (EAN) | 4032248257201                             |
| Qty.       | 2 m                                       |

**TS 27X12.5M/ST/F.ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 12.5 mm  | Depth (inches)  | 0.492 inch |
| Height     | 27 mm    | Height (inches) | 1.063 inch |
| Width      | 2,000 mm | Width (inches)  | 78.74 inch |
| Net weight | 50 g     |                 |            |

**Temperatures**

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

**Mounting rail**

|                             |                 |          |
|-----------------------------|-----------------|----------|
| Installation advice         | Direct mounting |          |
| Length of the terminal rail | max.            | 2,000 mm |
|                             | min.            | 0 mm     |
|                             | nominal         | 2,000 mm |
| Material                    | Steel           |          |
| Standards                   | DIN EN 60715    |          |
| Surface finish              | galvanized      |          |
| Thickness                   | 2 mm            |          |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001285    | ETIM 7.0    | EC001285    |
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ECLASS 9.0  | 27-40-06-02 | ECLASS 9.1  | 27-40-06-02 |
| ECLASS 10.0 | 27-40-06-02 | ECLASS 11.0 | 27-40-06-02 |
| ECLASS 12.0 | 27-40-06-02 | ECLASS 13.0 | 27-40-06-02 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |

## TS 27X12.5M/ST/F.ZN

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

