

SAIBW-M-5/8 M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

| | |
|------------|---|
| Version | Field attachable connector, M12, Socket, angled |
| Order No. | 1803920000 |
| Type | SAIBW-M-5/8 M12 |
| GTIN (EAN) | 4032248260232 |
| Qty. | 1 pc(s). |

SAIBW-M-5/8 M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|------|
| Net weight | 70 g |
|------------|------|

Technical data customisable plug-in connectors

| | | | |
|-------------------------------|----------------------|-------------------------------|----------------------|
| Cable diameter | 6...8 mm (PG9) | Cable diameter, max. | 8 mm |
| Cable diameter, min. | 6 mm | Coding | A-coded |
| Conductor cross-section, max. | 0.75 mm ² | Conductor cross-section, min. | 0.14 mm ² |
| Contact surface | Gold-plated | Housing main material | CuZn |
| Insulation strength | 10 ⁸ Ω | Number of poles | 5 |
| Plugging cycles | ≥ 100 | Pollution severity | 3 |
| Protection degree | IP67 | Rated current | 4 A |
| Rated voltage | 60 V | Shield connection | Yes |
| Temperature range of housing | -40 ... +85 °C | Threaded ring material | Diecast zinc |
| Type of connection | Screw connection | | |

General Info

| | | | |
|-------------------|-------|-----------------------|-------------|
| Number of poles | 5 | Connection 1 | M12 |
| Connection 2 | Screw | Housing main material | CuZn |
| Connection thread | M12 | Contact surface | Gold-plated |
| Protection degree | IP67 | Plugging cycles | ≥ 100 |

Standards

| | |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-101 |
|--------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002635 | ETIM 7.0 | EC002635 |
| ETIM 8.0 | EC002635 | ETIM 9.0 | EC002635 |
| ECLASS 9.0 | 27-44-01-02 | ECLASS 9.1 | 27-44-01-03 |
| ECLASS 10.0 | 27-44-01-02 | ECLASS 11.0 | 27-44-01-02 |
| ECLASS 12.0 | 27-44-01-16 | ECLASS 13.0 | 27-44-01-02 |
| ECLASS 14.0 | 27-44-01-16 | | |

Environmental Product Compliance

| | |
|--------------------------------------|---|
| REACH SVHC | Lead 7439-92-1 Imidazolidine-2-thione 96-45-7 |
| SCIP | bcee35cf-c0f5-43d2-8daf-65ab0d08641a |
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E307231 |

Creation date August 29, 2024 7:24:03 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

SAIBW-M-5/8 M12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Manual |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |

SAIBW-M-5/8 M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

