

**SAIB-4-IDC (0,75) M12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

**General ordering data**

Version	Field attachable connector, M12, Female socket, straight
Order No.	<a href="#">1852750000</a>
Type	SAIB-4-IDC (0,75) M12
GTIN (EAN)	4032248386871
Qty.	1 pc(s).

## SAIB-4-IDC (0,75) M12

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 39.98 g

## Technical data customisable plug-in connectors

Assignment	Pin 1 - 4	Cable diameter	5.5...8 mm
Cable diameter, max.	8 mm	Cable diameter, min.	5.5 mm
Coding	A-coded	Conductor cross-section, max.	0.75 mm <sup>2</sup>
Conductor cross-section, min.	0.34 mm <sup>2</sup>	Connection cross-section, max.	0.75 mm <sup>2</sup>
Connection cross-section, min.	0.34 mm <sup>2</sup>	Contact surface	tinned
Housing main material	CuZn	Insulation strength	10 <sup>8</sup> Ω
Number of poles	4	Plugging cycles	≥ 50
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	50 V
Shield connection	No	Temperature range of housing	-25...+85 °C
Threaded ring material	Diecast zinc	Type of connection	Insulation displacement connection

## General Info

Number of poles	4	Connection 1	M12
Connection 2	IDC	Description of article	SAIS / B IDC (0.75)
Housing main material	CuZn	Connection thread	M12
Contact surface	tinned	Protection degree	IP67
Plugging cycles	≥ 50		

## Standards

Connector standard IEC 61076-2-101

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

## Approvals

ROHS Conform

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

## SAIB-4-IDC (0,75) M12

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

**Pole scheme**

